


18in SATA to Right Side Angle SATA Serial ATA Cable

Product ID: SATA18RSA1



The SATA18RSA1 Right Side-Angled SATA Cable (18-inch) features one straight and one right side-angled (7-pin) data receptacle, which positions the cable so that it runs parallel to the drive ports – ideal for connectivity in narrow spaces, enabling installation of the drive as needed within the system case.

The cable also features a flexible low profile design that helps improve airflow and reduce clutter in your computer case, which helps keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance and reliability this 18" SATA cable supports full SATA 3.0 bandwidth (up to 6Gbps) when used with SATA 3.0 compliant drives and is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

Features

- 1x SATA connector

- 1x Right side-angled SATA connector
- Supports full SATA 3.0 6Gbps bandwidth
- Compatible with both 3.5" and 2.5" SATA hard drives
- Provides 18" in cable length

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Type and Rate	SATA III (6 Gbps)
---------------	-------------------

Connector(s)

Connector A	SATA (7 pin, Data)
Connector B	SATA (7 pin, Data)

Physical Characteristics

Color	Red
Wire Gauge	26 AWG (0.404 mm)
Cable Length	18.0 in [45.7 cm]
Product Length	18.0 in [45.7 cm]
Weight of Product	0.5 oz [15 g]

Packaging Information

Package Quantity	1
Package Length	9.1 in [23.2 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	0.6 oz [16.5 g]

What's in the Box



Included in Package 18in SATA to Right Side Angle SATA Serial ATA Cable

****Product appearance and specifications are subject to change without notice.***

