

Drive Docking Station for 2.5 / 3.5" SATA Drives - USB 3.1 (USB-A, USB-C) or eSATA

Product ID: SDOCKU313E



Connect and access any 2.5" or 3.5" SATA hard drive or SSD using this single-drive docking station, over a USB 3.1 Gen 2 (up to 10Gbps) or eSATA connection.

Ideal for IT professionals, the docking station lets you access a SATA solid-state drive or hard drive quickly, for drive imaging, data recovery, and backups.

You can connect through either USB 3.1 Gen 2 or eSATA, and take advantage of the high performance of the latest SSDs and HDDs.

The dock's vertical drive insertion makes it easy to dock and swap drives from your desktop computer or laptop. You simply insert your SSD or HDD into the drive slot at the top of the docking station, with no tools or trays required. The HDD ejection button allows fast and simple drive removal.

This single-bay docking station comes with a USB Type-A to Type-C cable, for connecting to newer USB-C enabled devices. It also comes with a USB Type-A to Type-B cable, providing backward compatibility with your existing USB 3.0, 2.0 and 1.x devices. An eSATA cable is also included with the dock.

The docking station is also UASP compatible, for enhanced performance.

The SDOCKU313E is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Get quick access to drives, ideal for system builders and IT professionals
- Back up data quickly to an archive drive
- Easily take backup data to an offsite location for safekeeping

Features

- Connect and access a 2.5" or 3.5" SATA SSD/HDD over USB 3.1 Gen 2 or eSATA
- Access drives at full speed with support for SATA I, II and III (up to 6Gbps)
- Top-loading design with built-in ejection button for easy drive access
- Tool-less and tray-less design
- Supports large drive capacity of up to 6TB
- USB Type-B to A cable included for backward compatibility with USB 3.0, 2.0 and 1.x
- UASP support for enhanced performance
- USB Type-B to C cable included for compatibility with USB-C enabled devices

Hardware	Warranty	2 Years
	Fan(s)	No
	Interface	USB 3.1 Gen 2
	Interface	eSATA
	Bus Type	USB 3.1 Gen 2 & eSATA
	Number of Drives	1
	Drive Size	2.5in & 3.5in
	Compatible Drive Types	SATA
	Drive Installation	Removable
	Chipset ID	ASMedia - ASM1351
Performance	Type and Rate	USB 3.1 Gen 2 - 10 Gbit/s
	UASP Support	Yes
	TRIM Support	Yes
	4Kn Support	Yes
	Type and Rate	SATA III (6 Gbps)
	Max Drive Capacity	Currently tested with hard drives up to 6TB at 7200 RPM
	Hot Swap Capability	Yes
Connector(s)	Drive Connectors	SATA Data & Power Combo (7+15 pin)
	Host Connectors	USB 3.1 USB Type-B (9 pin, Gen 2, 10 Gbps)
	Host Connectors	eSATA (7 pin, Data)
Software	OS Compatibility	OS independent; No software or drivers required

Special Notes / Requirements	Note	Windows 7 and earlier Windows versions do not support TRIM with USB to SATA devices.
Indicators	LED Indicators	Power & Activity
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.6 A
	Output Voltage	12V DC
	Output Current	2.0 A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	24
Environmental	Operating Temperature	5C to 35C (41F to 95F)
	Storage Temperature	-20C to 50C (-4F to 122F)
	Humidity	20% ~ 80% RH
Physical Characteristics	Color	Black
	Material	Plastic
	Product Length	5.7 in [1.4 cm]
	Product Width	3.7 in [93 mm]
	Product Height	2.5 in [63.4 mm]
	Weight of Product	14.5 oz [410 g]
Packaging Information	Package Length	6.7 in [1.7 cm]
	Package Width	6.3 in [1.6 cm]
	Package Height	3.6 in [91 mm]
	Shipping (Package) Weight	30.4 oz [862 g]
What's in the Box	Included in Package	USB 3.1 & eSATA HDD/SSD docking station
	Included in Package	universal power adapter (NA/JP, EU, UK, ANZ)
	Included in Package	3.3 ft. [1 m] USB-A to USB-B cable

Included in Package	3.3 ft. [1 m] eSATA cable
Included in Package	quick-start guide
Included in Package	3.3 ft. [1 m] USB-C to USB-B cable

****Product appearance and specifications are subject to change without notice.***

