

8ft (2.4m) Heavy Duty Power Cord, NEMA 5-15P to Right Angle C15, 15A 125V, 14AWG, Heavy Gauge PDU Power Cable, Replacement AC Power Cord, TAA Compliant, UL Listed

Produkt-ID: PXT515C158RA



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect a server or high-power rackmount equipment to a wall outlet or PDU

Merkmale

- **RIGHT ANGLE POWER CORD:** 8ft (2.44m) Heavy Duty Power Cable with NEMA 5-15P to Right Angle IEC 60320 C15 connector is suitable for servers or high-powered equipment; 90-degree C15 connectors facilitates access in tight spaces; Indoor use; Rated for 125V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully-molded connector strain relief for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 8ft (2.44m); TAA Compliant; NEMA 5-15P to Right Angle IEC 60320 C15; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Jacket Material: PVC; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA 5-15P plug works with North American electrical outlets and PDUs; IEC C15 connector works with servers, switches, and high-power rackmount appliances; Replacement heavy gauge power cable
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This NEMA 5-15P to C15 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Steckverbinderplatten Nickel

Typ der PVC
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1
e

Kabeltyp	SJT	
<hr/>		
Steckverbinder		
Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)	
Steckverbinder B	1 - IEC 60320 C15 Strom	
<hr/>		
Strom		
Eingangsspannung	125V AC	
Eingangsstrom	15A	
<hr/>		
Umgebungsbedingungen		
Betriebstemperatur	-20° to 105°C (-4° to 221°F)	
Lagertemperatur	-20° to 105°C (-4° to 221°F)	
Feuchtigkeit	0% to 65% RH	
<hr/>		
Physische Eigenschaften		
Farbe	Schwarz	
Steckverbinderart	Gerade auf rechtsgewinkelt	
Drahtstärke	14 AWG	
Kabellänge	8.0 ft [2.4 m]	
Außendurchmesser des Kabels	0.4 in [9 mm]	
Produktlänge	8.0 ft [2.4 m]	
Produktbreite	2.4 in [6.2 cm]	
Produkthöhe	1.6 in [4.2 cm]	
Produktgewicht	14.0 oz [396.0 g]	
<hr/>		
Verpackungsinformationen		
Paketlänge	11.4 in [29.0 cm]	

Paketbreite 5.7 in [14.5 cm]

Pakethöhe 1.6 in [4.0 cm]

Versandgewicht
(Verpackung) 14.3 oz [404.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - 2,4m NEMA 5-15P auf rechtwinkliges C15
Stromkabel

Garantieinformatio
nen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

