

Fiber Optic Cable - Single-Mode Duplex 9/125 - LSZH - ST/SC - 1 m

Product ID: SMFIBSTSC1



The SMFIBSTSC1 1m ST to SC Single-Mode Duplex Fiber Cable features 9/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex single-mode applications.

This ST-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire - an ideal solution for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 9/125 (OS1) Single-Mode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability, and is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Used by long distance networks with mission critical data
- Telecommunication/Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Features

- OS1 (9/125)

- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

Hardware

Warranty	Lifetime
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Size	9/125

Performance

Fiber Classification	OS1
Type	Single Mode

Connector(s)

Connector A	Fiber Optic ST Duplex
Connector B	Fiber Optic SC Duplex

Physical Characteristics

Color	Yellow
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.4 in [10 mm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	1.4 oz [40 g]

What's in the Box

Included in Package	1m Singlemode Duplex Fiber Cable ST-SC
---------------------	--



****Product appearance and specifications are subject to change without notice.***

