

Cisco QSFP-40G-LR4-S Compatible QSFP+ Module - 40GBASE-LR4 - 40GbE Single Mode Fiber SMF Optic Transceiver - 40GE Gigabit Ethernet QSFP+ - LC 10km - 1270nm to 1330nm - DDM  
Cisco Firepower, ASR1000, ASR9000

**Product ID:** QSFP40GLR4S



The QSFP40GLR4S is a Cisco QSFP-40G-LR4-S compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBASE-LR4 compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1270nm to 1330nm
- Maximum Data Transfer Rate: 40 Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 1,489,426 hours
- Power Consumption: Less than 2.5 Watts
- Digital Diagnostics Monitoring (DDM): Yes

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

- Replacing defective or damaged SFP+ modules in Cisco switches and routers
- Expand your network to remote segments

### Features

- **100% CISCO QSFP-40G-LR4-S COMPATIBLE:** Works with Cisco switches like Firepower, ASR1000, ASR9000, C9300, C3850 and others
- **TECHNICAL SPECS:** 40GBASE-LR4 40 Gbps Single Mode (SMF) LC Connector 1270nm to 1330nm Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24

---

#### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Industry Standards	IEEE 802.3ba 40GBASE-LR4

---

#### Performance

Maximum Data Transfer Rate	40 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1270nm to 1330nm
Fiber Operating Mode	Full-Duplex
DDM	Yes



Compatible Networks	40 Gbps
MTBF	1,489,426 hours
Power Consumption (In Watts)	< 2.5 W

---

#### Connector(s)

Local Unit Connectors	Fiber Optic LC Duplex
-----------------------	-----------------------

---

#### Special Notes / Requirements

Note	For use in 40 Gigabit fiber networking equipment and media converters
------	-----------------------------------------------------------------------

---

#### Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

---

#### Physical Characteristics

Product Length	2.8 in [72.0 mm]
Product Width	0.7 in [18.4 mm]
Product Height	0.5 in [13.0 mm]
Weight of Product	1.6 oz [44.0 g]

---

#### Packaging Information

Package Length	4.6 in [11.7 cm]
Package Width	3.6 in [92.0 mm]
Package Height	1.3 in [34.0 mm]
Shipping (Package) Weight	3.4 oz [95.0 g]

---

#### What's in the Box

Included in Package	QSFP+ transceiver
---------------------	-------------------

---

***\*Product appearance and specifications are subject to change without notice.***