

HDMI over CAT5e HDBaseT Extender - RS232 - IR - Ultra HD 4K - 330 ft (100m) - TAA

**Product ID:** ST121UTPHD2



The StarTech.com HDBaseT extender kit, extends HDMI up to 330 feet (100 Meters) over a single CAT5e or CAT6 cable. The extender supports Ultra HD and Full HD resolutions (4K / 1080p) with support for 3D and the accompanying 7.1 digital audio. For added versatility the transmitter and receiver can be used to transmit IR and RS232 serial communication over the same cable. The versatility of this video extender makes it an ideal solution for digital signage applications.

HDBaseT is a standardized, zero latency, video distribution technology that's revolutionizing HDMI distribution. HDBaseT uses an advanced method of modulation that enables you to distribute uncompressed HDMI audio and video along with additional signals such as 100BaseT Ethernet, IR, RS-232 serial and power over cable.

The extender offers HDBaseT technology with HDMI, IR, and RS232 control in a single CAT 5e extender kit, for complete end-to-end control. Offering greater versatility than traditional HDMI extenders or HDMI cabling alone HDBaseT is the clear choice for every integrator and system designer. The IR extension enables you operate your display and an IR-enabled source device, such as a Blu-ray player or TV Set top box, from either end of your extension. While RS232 control let you to connect a serial I/O device at your display - an ideal solution for adding a serial touch screen interface to your remote display.

With the A/V industry quickly adopting 4K as the new high-resolution video standard, long range video distribution can be a challenge with standard HDMI cables beginning signal degradation at 30 feet.

With support for 4K 30Hz you'll be amazed at how HDBaseT maintains your Ultra HD picture quality, four times the resolution of high-definition 1080p, even at 164 feet away from your video source. Plus, because the extender is still backward compatible with High-Definition 1080p displays and video sources, you can rest assured this extender will make your video source look great in any remote digital signage application.

This extender has been specially crafted for a smooth, tidy installation. HDBaseT technology allows for single cable installation, for seamless integration using existing CAT5e or CAT6 infrastructure, avoiding the hassle of running multiple cables, while reducing potential failure points. Mounting hardware is also built-in to both the extender and receiver for discrete, professional mounting.

The ST121UTPHD2 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Position a display/monitor in a convenient viewing area while the transmitting content over a CAT5 cable from a cleaner, more secure environment
- Ideal for digital signage applications in financial, educational, medical and business sectors
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at trade-shows and in auditoriums

## Features

- With HDBaseT extend HDMI, IR, and RS-232 through one CAT5e or CAT6 cable
- Astonishing picture quality with support for resolutions up to UltraHD 4K (up to 50m)
- Hassle-free installation with a single CAT5e or CAT6 cable and built-in mounting hardware
- Supports HD video resolutions such as 1920x1200 or 1080p at distances up to 330 ft. (100m)
- Supports unidirectional RS232
- Dolby TrueHD, DTS-HD MA Audio
- RS232 interface supports up to 115200bps full-duplex data rate
- No software or drivers required

---

### Hardware

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP or better

Audio	Yes
Industry Standards	High Speed HDMI and HDCP compliant
Daisy-Chain	No

---

## Performance

Maximum Data Transfer Rate	HDMI - 3.4Gbps
	RS232 - 115200bps baud
Max Distance	100m [328ft]
Maximum Digital Resolutions	4K
Supported Resolutions	3840x2160 (4K)
	2560x1600
	1920x1200
	1920x1080 (1080p)
	1280x720 (720p)
Wide Screen Supported	Yes
Audio Specifications	Supports Dolby TrueHD, DTS-HD MA
General Specifications	IR Interface: unidirectional
	38Khz / 10 / 5M

---

## Connector(s)

Local Unit Connectors	1 - DB-9 (9 pin, D-Sub)
	2 - HDMI (19 pin)
	1 - IrDA (Infrared, SIR/FIR)
	1 - RJ-45
Remote Unit Connectors	1 - DB-9 (9 pin, D-Sub)
	1 - HDMI (19 pin)
	2 - IrDA (Infrared, SIR/FIR)
	1 - RJ-45

---

## Software

	OS Compatibility	OS Independent
<hr/>		
<b>Special Notes / Requirements</b>		
	System and Cable Requirements	1X Standard CAT5 cable, 1X HDMI Cable for Remote Unit (Local Cable Included)
<hr/>		
<b>Indicators</b>	LED Indicators	1 - Power (Green)
		1 - RJ45 Link (Green)
		1 - Mode (Green)
		1 - HDCP (Green)
<hr/>		
<b>Power</b>	Power Source	2 AC Adapters Included
	Input Voltage	100 - 240 AC
	Input Current	0.6
	Output Voltage	12V DC
	Output Current	1.24A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	12
<hr/>		
<b>Environmental</b>	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-20C to 85C (-4F to 185F)
	Humidity	0-95%
<hr/>		
<b>Physical Characteristics</b>	Color	Black
	Material	Steel
	Product Length	5.9 in [15.0 cm]

Product Width	3.1 in [8.0 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	1.3 lb [0.6 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	10.0 in [25.4 cm]
Package Width	12.2 in [30.9 cm]
Package Height	2.6 in [6.7 cm]
Shipping (Package) Weight	3.4 lb [1.5 kg]

---

#### What's in the Box

Included in Package	1 - Local HDMI Extender Unit
	1 - Remote HDMI Receiver Unit
	1 - IR Receiver Cable
	1 - IR Transmitter Cable
	1 - HDMI Cable - 4 ft (1.2 Meters)
	2 - Universal Power Adapter NA / UK / EU
	1 - User Manual

---

***\*Product appearance and specifications are subject to change without notice.***