

3U 19in Steel Vertical Wall Mount Equipment Rack Bracket

Product ID: RK319WALLV



The RK319WALLV 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 3U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design, perfect for SoHo (small office, home office) environments. The wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com lifetime warranty.

Need more storage space? StarTech.com also offers a [%product id="RK119WALLV" text="1U 19in Wallmount Bracket"%], a [%product id="RK219WALLV" text="2U 19in Wallmount Bracket"%] and a [%product id="RK419WALLV" text="4U 19in Wallmount Bracket"%].

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space

- Ideal for small and medium businesses needing rack solutions

Features

- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability
- Compatible with most 19" rack mountable equipment
- Arrives fully assembled with cage screws and nuts for mounting equipment into the rack
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Equipment can be vertically wall mounted, or horizontally under a desk
- TAA compliant for GSA Schedule purchases

Hardware	Warranty	Lifetime
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	3U
	Mounting Rail Profile	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity	125.3 lb [56.7 kg]
Special Notes / Requirements	Note	Package includes 1 " screws for mounting to wood surfaces, additional hardware will be required for other materials
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Product Length	5.9 in [1.5 cm]
	Product Width	19.8 in [5.0 cm]
	Product Height	5.9 in [1.5 cm]
	Weight of Product	32.5 oz [921.018 g]
Packaging Information	Flat Pack (Assembly Required)	No
		20.4 in [5.2 cm]
	Package Length	6.5 in [1.6 cm]
	Package Width	6.3 in [1.6 cm]
	Package Height	3.0 lb [1.4 kg]

Shipping (Package)
Weight

**What's in the
Box**

Included in Package	Vertical Wall Mount Bracket
Included in Package	Wood Screws
Included in Package	M5 Screws
Included in Package	M5 Cage Nuts
Included in Package	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

