

4U 19in Secure Horizontal Wall Mountable Server Rack - 2 Fans Included

Product ID: RK419WALVSGB



The RK419WALVSGB 4U 19-inch Secure Horizontal Wall-Mountable Server Rack is a lockable, solid steel storage rack that provides a robust solution for wall mounting telecom, network or server equipment, and includes two 120mm fans, for improved airflow. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 4U rack can be mounted to a wall in a server room, office, or above a doorway in rooms lacking the space for a full-size rack, to expand your workspace and keep your equipment protected from unauthorized access. The bracket mounting holes (used to mount to a wall or desk) are positioned at 16-inches apart, matching standard stud measurements for easy installation.

Constructed to EIA-RS310 standards, the wallmount server rack allows equipment to be mounted horizontally, and offers a hinged lockable front cover as well as a lockable body. Alternatively, non-rackmount equipment can be mounted vertically with the included bottom cover, using the rack as a wall case.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter

- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Includes optional 4U steel plate which acts as a shelf, allowing the rack to be used as a wall case for any non-rackmount equipment
- Hinged, lockable front cover
- TAA compliant for GSA Schedule purchases
- Both the top cover and the rack body are lockable separately for varying security levels
- 2 x 120mm fans included
- Wall mounting holes are 16in center to center, for greater stability and mounting to standard wall studs
- Compatible with most 19in wide rack-mountable equipment
- Solid steel construction
- Constructed to meet the EIA-RS310 19in rack standards

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Steel
U Height	4U
Special Features	Grounding Lug(s)
	Lockable Top Hatch
	Ships Fully Assembled
	Wall-Mountable
Mounting Rail Profile	L-Shape
Fan Options	Two Fans Included: 120 mm

Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Airflow Rate	106 CFM
Audible Noise	46 dBA @ 1 Meter
Weight Capacity	149.9 lb [68 kg]

Physical Characteristics

Color	Black
Front Door Construction	Steel
Front Door Features	Secure Key Lock with Removable Front Door
Side Panel Construction	Steel

Product Measurements

Internal Width	19.1 in [48.5 cm]
Internal Depth	23.0 in [58.5 cm]
Product Length	25.4 in [64.4 cm]
Product Width	28.4 in [72.1 cm]
Product Height	8.6 in [21.9 cm]
Weight of Product	43.9 lb [19.9 kg]
Maximum Mounting Depth	20.5 in [52.1 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	30.5 in [77.4 cm]
Package Width	28.0 in [71.0 cm]
Package Height	11.3 in [28.8 cm]
Shipping (Package)	50.9 lb [23.1 kg]

Weight

What's in the Box

Included in Package	1 - RK419WALVS 4U Wallmount Rack
	1 - Set of Keys
	1 - UK to EU Plug Converter
	24 - #10-32 Screws
	24 - #10-32 Cage Nuts

****Product appearance and specifications are subject to change without notice.***