

Dual Port PCI Express Gigabit Ethernet PCIe Network Card Adapter - PoE/PSE

Product ID: ST2000PEXPSE




The ST2000PEXPSE Dual Port PoE NIC provides two 10/100/1000 Mbps PoE RJ45 ports that can provide up to 25.5W of power each, combining a network data connection and power on a single cable, for less clutter and convenient installations in remote locations.

This full/low profile Gigabit server adapter supports the IEEE 802.3at (Type 1 and 2) standard for a Power Sourcing Equipment (PSE) device, and can deliver 48V DC power to compliant Powered Devices (PD). This eliminates the need for a separate power source and cable for remote networked devices such as IP cameras, IP phones and wireless access points.

Suitable for any PCI Express-enabled client, server or workstation, this versatile PoE network adapter supports features such as Jumbo Frames, VLAN tagging and Wake on LAN (WOL).

The ST2000PEXPSE PoE NIC is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add 2 Ethernet ports to a workstation or server computer from a single PCIe slot
- Connect to 2 separate networks simultaneously
- Install dual networking capabilities into a small form factor or other space-constrained computer system

- Provide power to PoE powered devices, where they have no access to a power source
- Connecting Power over Ethernet-enabled IP cameras, IP phones or Wireless Access Points

Features

- Dual 10/100/1000 Mbps PoE RJ45 ports
- Built-in SATA and LP4 Molex power connector
- Supports IEEE 802.3at (Type 1, 2) Power over Ethernet standard
- Jumbo Frame support
- On-chip 48 KB Big Transmit/Receive Buffer Support
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, and supports IEEE 802.1Q VLAN tagging, IEEE 802.1P Layer 2 Priority Encoding and IEEE 802.3x Full Duplex Flow Control
- Crossover Detection & Auto-Correction (Auto MDIX)
- Includes full and low profile/half-height installation brackets
- Power Sourcing Equipment (PSE) design, provides data and up to 25.5W of power on each port
- Unique surge protection design helps prevent system damage in the event of lightning strikes

Hardware	Warranty	2 Years
	Ports	2
	Interface	RJ45 (Gigabit Ethernet)
	Bus Type	PCI Express
	Card Type	Standard Profile (LP bracket incl.)
	Port Style	Integrated on Card
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, IEEE 802.3at
	Chipset ID	Realtek - RTL8111E
Performance	Maximum Data Transfer Rate	1000 Mbps (uni-directional), 2000 Mbps (bi-directional)
	Buffer Size	48 KB
	Compatible Networks	10/100/1000 Mbps
	Auto MDIX	Yes
	Full Duplex Support	Yes
	MTBF	140,981 hours
Connector(s)	Connector Type(s)	PCI Express x1
	Internal Ports	LP4 (4 pin; Large Drive Power)
	Internal Ports	SATA Power (15 pin)
	External Ports	RJ-45
Software	OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10

Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019

Mac OS X 10.6 to 10.9
Linux 2.4.x to 4.11.x <i>LTS Versions Only</i>

Special Notes / Requirements	Patents and Licenses	The following patents are licensed for this product. This list might not be all inclusive.
	System and Cable Requirements	<ul style="list-style-type: none"> • United States Patent No. 5,406,260 (expired)
	System and Cable Requirements	<ul style="list-style-type: none"> • United States Patent No. 6,650,622 • United States Patent No. 7,457,250 • United States Patent No. 8,155,012 • United States Patent No. 8,902,760 • United States Patent No. 8,942,107 • United States Patent No. 9,019,838 • United States Patent No. 9,049,019 • United States Patent Application No. 14/695,456 • United States Patent Application No. 14/726,940
		Available full/low profile PCI Express expansion slot
		Available LP4 Molex or SATA power connector

Indicators	LED Indicators	Link/ Activity (green)
	LED Indicators	PoE Active (yellow)

Power	Output Voltage	48 DC
--------------	----------------	-------

Environmental	Operating Temperature	0C to 55C (32F to 131F)
	Storage Temperature	-20C to 85C (-4F to 185F)
	Humidity	5% ~ 95% RH

Physical Characteristics	Product Length	7.7 in [2.0 cm]
	Product Width	0.7 in [19.000 mm]
	Product Height	2.7 in [68.000 mm]
	Weight of Product	3.7 oz [104.000 g]

Packaging Information	Package Length	6.5 in [1.6 cm]
	Package Width	9.1 in [2.3 cm]



Package Height	1.8 in [45.000 mm]
Shipping (Package) Weight	8.7 oz [246.000 g]

What's in the Box	Included in Package	Low Profile Bracket
	Included in Package	Instruction Manual
	Included in Package	PCI Express Network Card
	Included in Package	Driver CD

****Product appearance and specifications are subject to change without notice.***

