

2-Post 6U Wall Mount Network Cabinet with Acrylic Door, 19" Wall-Mounted Server Rack for Data / AV / Electronics / Computer Equipment, Small Vented Rack Enclosure

Produkt-ID: RK619WALL



StarTech.com

The RK619WALL Wall Mounted 6U Server Rack/Cabinet can be fastened to most types of walls and features a sturdy, compact design that can be positioned almost anywhere without wasting valuable floor space.

This equipment rack offers 6U of storage space and is designed to accommodate 19-inch (wide) servers, networking and telecom equipment. The rack features a 12cm fan, with ventilation positioned above and below the front panel glass door, helping to keep dust out of the rack while ensuring a cool operating environment for your valuable equipment.

To ensure optimum security and prevent tampering with the enclosed equipment, the cabinet/rack features a lockable acrylic front door that can be removed entirely or installed to open to the left or right as needed.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Install rack equipment over doorways, or in tight spaces like server closets
- Mount networking and telecommunication equipment to the wall

- Securely protect and wall mount sensitive rack mountable equipment

Merkmale

- Abschließbare Tür aus Acrylglas mit großem Sichtbereich
- EASY ACCESS: Wall-mount data rack features an enclosed and lockable rack design with easy access to the rear of the mounted devices; Small locking server cabinet with reversible and removable front door and removable side panels
- TAA-konform für GSA Schedule-Käufe
- Belüftete Seitenwände mit einem 120 mm großen Kühllüfter
- Große Kabeldurchführungen mit Kabeltüllen in den Seitenwänden und auf der Unterseite

Hardware

Garantiebestimmungen	Lifetime
Wandmontierbar	Ja
Rack-Typ	2-Pfosten
Rahmentyp	Geschlossener Schrank
U-Höhe	6U
Besondere Funktionen	Wird vollständig montiert geliefert Wandaufhängung möglich
Montageschienenprofil	L-Shape
Kühlungsoptionen	Ein Lüfter im Lieferumfang enthalten: 120 mm + ein optionaler Lüfter: 120 mm
Mounting Hole Types	Quadratisch (für Käfigmuttern)
Industrienormen	EIA/ECA-310-E

Leistung

Airflow Rate	82 CFM
Hörbares Geräusch	38 dbA bei 1 Meter
Weight Capacity	110.2 lb [50 kg]

Physische Eigenschaften

Farbe	Schwarz
Frontdoor-Typ	Stahl mit Fenster
Merkmale der Vorderklappe	Sicherheitsschloss mit abnehmbarer Vorderklappe
Seitenblendentyp	Stahl

Product Measurements

Interne Breite	21.7 in [55 cm]
Interne Tiefe	15.7 in [40 cm]
Produktlänge	15.7 in [40.0 cm]
Produktbreite	22.0 in [56.0 cm]
Produkthöhe	13.0 in [33.0 cm]
Produktgewicht	27.7 lb [12.6 kg]
Max. Montagetiefe	11.8 in [30 cm]

Verpackungsinformationen

Flache Verpackung (Montage erforderlich)	Nein
Paketlänge	26.4 in [67.0 cm]
Paketbreite	19.7 in [50.0 cm]
Pakethöhe	17.3 in [44.0 cm]
Versandgewicht (Verpackung)	33.5 lb [15.2 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 6U Wallmount Cabinet
	1 - Schlüsselset

20 - M5-Schrauben

20 - M5-Käfigmuttern

Garantieinformatio
nen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.