

Rackmount PDU with 16 Outlets and Surge Protection - 1U

Produkt-ID: RKPW161915



This 16-outlet (120V 15A)(12A UL) Rack PDU delivers a cost-effective power distribution solution for your server rack/cabinet. The 1U PDU can be mounted horizontally in any server rack 4in in depth or greater, to provide sixteen 120V 15A power ports/outlets, and features a rugged steel casing to ensure maximum durability.

The front of the PDU features two LEDs that indicate proper ground and surge detection, while enabling you to control the power state with an illuminated power/reset switch.

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in circuit breaker and reset switch, ensuring dependable performance of vital equipment.

Zertifikate Berichte und Kompatibilität



Anwendungen

- 16 easily accessible power outlets in a compact 1U of rack space
- Localize the power control for all of your connected system

Merkmale

- **CONVENIENT LAYOUT:** This rack-mount 16-outlet (120V) NEMA 5-15 power strip features a steel chassis, 6 ports on the front, and 10 ports on the back, so you can easily plug devices in and manage cables
- **SCALABLE:** This 1U rack mount PDU is ideal for small rack setups with only a few devices, allowing for plenty of future expansion, and features a 6 ft long cord so you can move your rack around
- **EASY INSTALLATION:** This rackmount PDU supports 19 inch rack 1U horizontal installation; Features LED indicators for ground and surge detection, a built-in circuit breaker, surge protection, and meets ANSI/EIA RS-310-D standards
- **BROAD COMPATIBILITY:** 1U horizontal rack-mounted power distribution unit fits many network / data 2-post and 4-post racks; Compatible with 19" server racks with minium 4" (10.2cm) depth
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this rack PDU is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	2 Years
Form Factor	Horizontal
Steckdosenkompatibilität	16
Einbaufähig	Ja

Leistung

Allgemeine Spezifikationen	Surge Protection: 1800 Joules
MTBF	207652 hours
Max. Eingangsstrom pro Phase	15A
Max. Gesamtstromaufnahme pro Phase	15A
Behördlich herabgesetzter Eingangsstrom (Nordamerika)	12A
Nominale Eingangsspannung	120V
Nominale	120V

Ausgangsspannung

Max. Ausgangsspannung 125V

Belastbarkeit 1800VA

Steckverbinder

Eingangssteckverbinder 1 - NEMA 5-15 Strom (Nordamerika)

Ausgangssteckverbinder 16 - NEMA 5-15 Strom (Nordamerika)

Anzeiger

LED-Anzeiger 1 - Ground

1 - Surge

Strom

Eingangsspannung 120 AC

Umgebungsbedingungen

Betriebstemperatur -5°C to 45°C (23°F to 113°F)

Lagertemperatur -25°C to 65°C (-13°F to 149°F)

Feuchtigkeit 0% RH

Physische Eigenschaften

Farbe Schwarz

Gehäusetypp Stahl

Kabellänge 6.0 ft [1.8 m]

Produktlänge 19.0 in [48.3 cm]

Produktbreite 3.8 in [9.6 cm]

Produkthöhe 1.7 in [4.3 cm]

Produktgewicht 4.4 lb [2.0 kg]

Verpackungsinform

ationen

Paketmenge	1
Paketlänge	9.3 in [23.5 cm]
Paketbreite	20.3 in [51.6 cm]
Pakethöhe	2.6 in [6.6 cm]
Versandgewicht (Verpackung)	4.9 lb [2.2 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 16 Port Stromverteiler
	1 - Installationshandbuch

Garantieinformatio
nen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.