

24in SATA Serial ATA Data and Power Combo Cable

Product ID: SATA24POW



The SATA24POW SATA Data and Power Cable features a combination 22-pin SATA receptacle data and power connector as well as an Molex (LP4) power connector and SATA receptacle data connector, allowing you to create a conventional Serial ATA data connection to a computer while powering the drive through an LP4 connection to the computer power supply.

This high quality SATA power/LP4 adapter cable measures 24in, providing the flexibility required to position the SATA hard drive as needed within the computer case, while eliminating the expense of upgrading the computer power supply for the sake of SATA compatibility.

Constructed of only top quality materials and designed for optimum performance and reliability this 24" SATA data and power combo cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- Connections to SATA Drive Arrays

Features

- 1x SATA (Data & Power) Receptacle
- 1x Molex (LP4) Power Connector

- 1x SATA Data Receptacle
- Supports full SATA 3.0 6Gbps bandwidth
- Compatible with both 3.5" and 2.5" SATA hard drives
- Provides 24" in cable length

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Type and Rate	SATA III (6 Gbps)
---------------	-------------------

Connector(s)

Connector A	SATA (7 pin, Data)
	LP4 (4 pin; Large Drive Power)
Connector B	SATA Data & Power Combo (7+15 pin)

Physical Characteristics

Color	Red
Connector Style	Straight
Cable Length	24.0 in [61.0 cm]

Packaging Information

Package Length	7.9 in [20 cm]
Package Width	3.2 in [81 mm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	1.4 oz [40 g]

What's in the Box

Included in Package	24in SATA Serial ATA Data and Power Combo Cable
---------------------	---

****Product appearance and specifications are subject to change without notice.***

