

## 2 Port DVI USB KVM Switch with Audio and USB 2.0 Hub

Product ID: SV231DVIUA



The SV231DVIUA 2-Port DVI USB KVM Switch lets you control two USB-enabled, DVI-capable computers from a single monitor and peripheral set (keyboard, mouse and speakers), and two additional USB peripherals connected through the built-in USB hub ports.

Featuring convenient hot-key and front panel push-button switching, and high-resolution support (up to 1920x1200), the DVI KVM Switch is perfect for controlling high-performance systems. Ideal for multimedia applications, this KVM switch supports audio and microphone switching either independently, or simultaneously when switching between computers for KVM control.

The DVI USB KVM also features an integrated USB 2.0 hub, which lets you share USB peripherals point as if they were connected directly to the slave computers.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Control two multimedia computers with a single set of console peripherals (Keyboard, Mouse, and two Monitors)
- Integrated USB 2.0 hub and Mic/Audio ports allow the user to have full multimedia control of two computers and share USB peripherals in a home office
- Dual system control for single user workstations, increasing user productivity in the office

### Features

- Stereo audio and microphone support
- Hot-key and front-panel push buttons for easy computer selection
- Supports resolutions up to 1920x1200
- HDCP Compliant
- Independent/simultaneous audio channel and PC port selection
- USB keyboard and mouse console connections
- No software or drivers required
- OS independent
- Built-in USB 2.0 hub

---

<b>Hardware</b>	Warranty	3 Years
	Audio	Yes
	KVM Ports	2
	PC Interface	USB
	PC Video Type	DVI
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	No
	Daisy-Chain	No

---

<b>Performance</b>	On-Screen Display	No
	DVI Support	Yes
	IP Control	No
	Hot-Key Selection	Yes
	Maximum Digital Resolutions	1920 x 1200 @60/70 Hz
	Maximum Number of Users	1 Push Button and Hotkeys
	Port Selection Support	126397 hours
	MTBF	

---

<b>Connector(s)</b>	Console Interface(s)	DVI-I (29 pin)
	Console Interface(s)	USB Type-A (4 pin) USB 2.0
	Console Interface(s)	3.5 mm Mini-Jack (3 Position)
	Host Connectors	DVI-I (29 pin)
	Host Connectors	USB B (4 pin)
	Host Connectors	3.5 mm Mini-Jack (3 Position)



<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Power</b>	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.8A
	Output Voltage	12V DC
	Output Current	1.5A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	18
<b>Environmental</b>	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0%~80%
<b>Physical Characteristics</b>	Color	Black
	Material	Steel
	Product Length	6.3 in [1.6 cm]
	Product Width	3.9 in [100 mm]
	Product Height	1.6 in [40 mm]
	Weight of Product	22.9 oz [650 g]
<b>Packaging Information</b>	Package Length	7.4 in [1.9 cm]
	Package Width	9.5 in [2.4 cm]
	Package Height	3.6 in [91 mm]
	Shipping (Package) Weight	2.3 lb [1.1 kg]
<b>What's in the Box</b>	Included in Package	2 Port DVI KVM Switch
	Included in Package	Universal Power Adapter (US/UK/EU)
	Included in Package	User Manual
	Included in Package	Pack, rubber feet

***\*Product appearance and specifications are subject to change without notice.***

