

S-Video / Composite to USB Video Capture Cable w/ TWAIN and Mac Support

Product ID: SVID2USB23



The SVID2USB23 USB 2.0 S-Video & Composite Video Capture Cable offers an easy to use analog video capture solution, enabling you to grab video from an S-Video or Composite video source, as well as the accompanying 2-channel RCA audio, to your Mac or Windows computer.

The cable connects to your desktop or laptop computer through USB 2.0, and is compact enough to fit in the palm of your hand, providing a conveniently portable video capture solution that's more than suitable for use with laptops and desktop computers alike.

An easy-to-use device for recording analog video to your computer from external sources, such as a VCR or camcorder the SVID2USB23 offers the perfect solution for Betamax or VHS video capture, with real-time MPEG-1, MPEG-2, and MPEG-4 encoding, as well as TWAIN support, to ensure compatibility with a wide range of systems and software.

This analog video capture cable supports a broad range of operating systems, delivering seamless analog video capture for Mac computers (OS 10.X), and Windows PCs (Windows 7/8/8.1/10, Windows 2000/XP(32/64-bit)/Vista(32/64-bit)).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Convert VHS home movies to digital format - Connect your VCR, camcorder, or any other analog video source to your Mac or PC and capture your audio/video in MPEG 1/2/4 format
- Import recorded videos onto your Mac or Windows computer for editing, and make your own compilation

Features

- Choose from MPEG-1, MPEG-2, or MPEG-4 video encoding
- Features TWAIN support for use with various software titles
- Plug and Play device installation, requires no power adapter
- Small and lightweight design offers convenient portability for on-the-go applications
- Snapshot function allows you to capture still images from video
- Supports NTSC, PAL, and SECAM video capture
- Up to 30 fps analog video capture capability at maximum resolution of 720x480(NTSC) / 720x576(PAL)
- Works with Mac or Windows computers

Hardware


Warranty	2 Years
AV Input	Audio RCA Composite S-Video
AV Output	USB
Audio	Yes
Industry Standards	NTSC, PAL, SECAM Video Encoding: MPEG 1, MPEG 2, and MPEG 4 DirectShow Compatible
Chipset ID	eMPIA - EM2861

Performance

Maximum Data Transfer Rate	480Mbps
Maximum Analog Resolutions	720x480(NTSC) / 720x576(PAL)

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
-------------	----------------------------



Connector B	S-Video (4 pin, Mini-DIN)
	Composite Video (1 x RCA)
	Stereo Audio (2 x RCA)

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10
	Apple OSX 10.6 - 10.14

Special Notes / Requirements

Note	The MPEG 4 video file format is supported on the included SVID2USB23 Capture software for Mac and other third party DirectShow capture software such as OBS
	movavi video software does not support the MPEG4 video file format

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5~85% RH Non-condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	20.7 in [52.7 cm]
Product Length	3.1 in [80.0 mm]
Product Width	1.3 in [34.0 mm]
Product Height	0.6 in [14.0 mm]
Weight of Product	2.3 oz [66.0 g]

Packaging Information

Package Length	5.7 in [14.6 cm]
Package Width	8.2 in [20.8 cm]



Package Height	1.6 in [41.0 mm]
Shipping (Package) Weight	6.2 oz [177.0 g]

What's in the Box

Included in Package	Driver CD
	Instruction Manual
	USB Video Capture Cable
	Software CD

****Product appearance and specifications are subject to change without notice.***

