

2.6ft (80cm) Right Angle Thunderbolt 5 Cable, 80Gbps/Up to 120Gbps, 240W PD, 8K 60Hz, Certified Thunderbolt Cable, Compatible w/Thunderbolt 4/USB4/USB-C

Product ID: TBLT5MM80CM240WRA



Experience reliable, ultra-high performance between Thunderbolt 5-enabled devices, supporting up to twice the bandwidth of Thunderbolt 4, 8K 60Hz video, and 240W charging over a single connection. This Thunderbolt 5 cable is ideal for high-performance laptops such as 16in MacBook Pro with M4 Pro/Max.

Transfer high-speed data and drive dual UHD displays with 80 Gbps bidirectional bandwidth. When higher bandwidth is required, Thunderbolt 5 Boost Mode reallocates the data lanes, enabling 120 Gbps (transmit) and 40 Gbps (receive). This asymmetric configuration is ideal for display-intensive tasks, such as driving multiple 8K monitors or handling high-resolution video workflows while still supporting robust data transfer capabilities.

Connect this Intel Thunderbolt-certified cable for guaranteed Thunderbolt 5 performance and backward compatibility. Certified cables ensure seamless operation across multiple resolutions, refresh rates, and resource-intensive applications.

The Right Angle Thunderbolt 5 cable features a flexible TPE outer jacket that is tested to withstand 2,000 bending cycles. Position the right angle connector along the device to reduce cable clutter and avoid prolonged strain from bending. The durable Nickel-plated connectors are rated to operate beyond 10,000 insertions.

This Certified Thunderbolt 5 Cable supports full Thunderbolt 5 performance:

- 80 Gbps bidirectional bandwidth, doubling the capacity of Thunderbolt 4
- 120 Gbps boost mode for display-intensive applications
- DisplayPort 2.1 Alt Mode: Up to 8K 60Hz/4K 240Hz video with DSC, HDR, and 10-bit color
- PCI Express 4.0 (64 Gbps) support for GPUs, NICs, and storage in PCIe chassis
- 240W Power Delivery EPR for charging for high-performance laptops
- Backward Compatibility with Thunderbolt 4/3, USB4 (40 Gbps), and USB 3.2 (10 Gbps)

This versatile Thunderbolt 5 cord is constructed with braided alloy shielding to minimize EMI for seamless and consistent data/video output and long-term reliable performance.

Certifications, Reports and Compatibility



Applications

- Support full Thunderbolt 5 capabilities between Thunderbolt 5-enabled devices
- Deliver up to 8K 60Hz video, 240W charging, and 80Gbps bidirectional throughput over a single connection
- 120Gbps boost mode supports multiple UHD displays while maintaining consistent data transfer rates
- Intel Certified Thunderbolt 5 Cable for guaranteed Thunderbolt 5 performance and backward compatibility with Thunderbolt 4/3, USB4, and USB-C
- Right Angle connector is ideal for space-constrained setups, allowing the cable to run flush with the device

Features

- **Unlock Thunderbolt 5 Capabilities:** Experience the full potential of Thunderbolt 5 with 80Gbps bandwidth (boosting to 120Gbps for display-intensive tasks), 240W Charging for power hungry laptops, and support for up to Dual 8K 60Hz over a single connection
- **Certified Performance & Reliability:** Intel-certified for Thunderbolt 5 performance with laptops like MacBook Pro with M4 Pro and Max; Ensure seamless backward compatibility with Thunderbolt 4 / 3, and USB4 hosts in mixed-hardware environments
- **Enable Intensive Pro Workflows:** Support advanced 8K visuals, fast refresh rates, vivid HDR with DP 2.1 Alt Mode (DSC, 10-bit color), and achieve 64Gbps PCIe 4.0 throughput for fast GPU, NIC, and external storage performance
- **Durable Right-Angle Design:** Right-angle Thunderbolt 5 connector reduces stress from sharp bends; Shielded 30/34AWG coaxial conductors minimize interference and maintain signal integrity; Durable halogen-free TPE jacket is ideal in busy work environments
- **The IT Pro's Choice:** Our Thunderbolt 5 cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

General

UPC

065030917490

	Warranty	Lifetime
Power		
	Power Delivery	240W
Physical & Environmental		
	Color	Black
	Connector Style	Straight to Right Angle
	Wire Gauge	30/34 AWG
	Cable Length	31.5 in [80 cm]
	Cable OD	0.2 in [4.7 mm]
	Product Length	32.0 in [81.3 cm]
	Product Width	0.6 in [14.6 mm]
	Product Height	0.3 in [6.5 mm]
	Weight of Product	1.3 oz [36 g]
	Operating Temperature	10C to 40C (50F to 104F)
	Storage Temperature	-10C to 50C (14F to 122F)
	Humidity	85% RH
Performance		
	Maximum Data Transfer Rate	80Gbps
	Maximum Digital Resolutions	8K 60Hz
	Video Revision	DisplayPort 2.1
Hardware		
	Active or Passive Adapter	Passive
	Connector Plating	Nickel
	Cable Shield Material	Tinned Copper Braid
Packaging & In-the-Box		

Included in Package	1 - Thunderbolt 5 Cable
Package Width	4.3 in [11 cm]
Package Depth	4.9 in [12.5 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	1.3 oz [36 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	USB-C (Thunderbolt 80Gbps)
Connector 2 (Quantity)	1
Connector 2	USB-C (Thunderbolt 80Gbps)

****Product appearance and specifications are subject to change without notice.***