

3 ft Mini USB Cable - A to Right Angle Mini B

Product ID: USB2HABM3RA



The USB2HABM3RA3ft USB to Right Angle Mini USB Cable provides a high quality connection between your Mini USB 2.0 mobile devices (smartphones, GPS, digital cameras, portable hard drives, etc.) and your PC or Mac computer, for everyday tasks such as charging, data synchronization or file transfers.

The right-angled Mini USB connector allows you to access your Mini USB devices, while keeping the cable out of the way, and stress away from the port.

Designed and constructed for maximum durability, this high quality USB to Mini USB cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a [3ft USB A to Left Angle Mini B Cable](#) (USB2HABM3LA), which provides the same convenience as this right-angled cable, but allows you to connect to your Mini USB device from the opposite direction.

Certifications, Reports and Compatibility



Applications

- Transfer data and provide power while charging your Mini USB device, without the cable getting in the way

Features

- Supports high-speed data transfer rates of up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief

Hardware	Warranty	1 Year
	Cable Jacket Material	PVC - Polyvinyl Chloride
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB Mini-B (5 pin)
Environmental	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	36.0 in [9.1 cm]
	Product Length	36.0 in [9.1 cm]
	Weight of Product	0.9 oz [26.308 g]
Packaging Information	Package Quantity	1
	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.3 in [8 mm]
	Shipping (Package) Weight	1.1 oz [31.071 g]
What's in the Box	Included in Package	3 ft Mini USB Cable - A to Right Angle Mini B

**Product appearance and specifications are subject to change without notice.*

