

3 ft USB Y Cable for External Hard Drive - USB A to mini B

Product ID: USB2HABMY3

The USB2HABMY3 3ft USB-A to Mini-B Y cable features two USB-A male connectors and a single USB Mini-B male connector - an ideal solution for providing additional power to your mini-USB external hard drive by connecting to two USB-A ports on your computer or laptop.

Especially valuable in situations where a single USB 2.0 port may not offer sufficient power to external hard drives, the USB2HABMY3 can be connected to two ports on one PC to increase the power output to power the external device.

This 3 ft cable is backed by StarTech.com's lifetime warranty for guaranteed dependability.

Certifications, Reports and Compatibility

Applications

- Connect an external 2.5in hard drive enclosure to a PC or laptop
- Provides both power and data connections between a host computer (Desktop, laptop) and an external USB storage device

Features

- 2x USB-A male connectors
- 1x USB Mini-B male connector
- Supports USB 2.0 data transfer rates up to 480Mbps
- Molded connectors with strain relief

Hardware	Warranty	Lifetime
	Cable Jacket Material	PVC - Polyvinyl Chloride

Performance	Type and Rate	USB 2.0 - 480 Mbit/s
--------------------	---------------	----------------------

Connector(s)	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB Mini-B (5 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Wire Gauge	24/28 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	2.0 oz [56.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	2.2 oz [62.0 g]

What's in the Box

Included in Package	3ft USB Y Cable
---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***

