

USB VGA and DVI Dual Port External Video Adapter

Product ID: USB2VGADVI



The USB2VGADVI USB to VGA/DVI-I adapter turns a USB 2.0 port into both a DVI-I and VGA video output port. Similar to our existing , the USB2VGADVI offers a convenient and cost-effective solution for adding multiple monitors to your computer without having to open the computer case for typical video card installation.

The video output ports on the USB to DVI/VGA adapter can be used simultaneously to extend your desktop or clone an image on two displays - essentially turning a USB connection into a dual head external video card.

The adapter features one DVI-I (out) port, one VGA (out) port, and two built-on USB ports that can be used as a USB hub, not only delivering simple external video but also allowing more USB peripherals to be installed on the host computer.

Certifications, Reports and Compatibility

Applications

- Add multiple monitors / projectors to your computer without the hassle of upgrading to a new video card
- In the office: View large or multiple spreadsheets across two screens

Features

- Offers a VGA and DVI-I (analog or digital) port for a dual monitor solution right out of the box.
- Supports resolutions up to 1680x1050 in 32bits.
- Works as a dual display hub and a 2 port USB hub.

- Works with laptops and desktop computers.
- Easy to use drivers and software enabling dual display applications

Hardware

Warranty	2 Years
AV Input	USB 2.0
AV Output	VGA DVI
USB Pass-Through	No
Memory	32MB
Chipset ID	Trigger - Trigger 1+

Performance

Supported Resolutions	1600x1200, 1680x1050, 1440x900, 1400x1050, 1360x768, 1280x1024, 1280x960, 1280x768, 1280x720, 1152x864, 1024x768 @ 16/32 bit
-----------------------	--

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	DVI-I (29 pin) VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows 8/8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64) Drivers are WHQL certified
------------------	--

Special Notes / Requirements

System and Cable Requirements	System Processor: 1.2GHz System Memory: 512MB
-------------------------------	--



Note

This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Indicators

LED Indicators	Power (Green)
----------------	---------------

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Output Voltage	5 DC
Center Tip Polarity	Positive
Plug Type	M

Environmental

Operating Temperature	0-70 degrees C
Storage Temperature	15-30 degrees C

Physical Characteristics

Color	Black
Product Length	3.4 in [86 mm]
Product Width	5.3 in [13.5 cm]
Product Height	0.7 in [18 mm]
Weight of Product	6.1 oz [172 g]

Packaging Information

Package Length	9.2 in [23.4 cm]
Package Width	2.7 in [68 mm]



Package Height	7.1 in [18 cm]
Shipping (Package) Weight	23.3 oz [660 g]

What's in the Box

Included in Package	USB to VGA and DVI Adapter
	Universal Power Adapter (US/UK/EU)
	Driver CD
	Instruction Manual
	3ft Mini USB to USB Cable

****Product appearance and specifications are subject to change without notice.***

