

## 1-Port 10G Ethernet Network Card - PCI Express - Intel X550-AT Chip

Product ID: ST10000SPEXI



Here's a powerful and cost-effective solution for upgrading your server or workstation to 10 Gigabit Ethernet networking over copper. This PCI Express 10G NIC lets you add an Ethernet port to your server or desktop computer and access your network at multiple speeds: 10G, 5G, 2.5G 1G and 100Mbps.

This 10G network card utilizes the Intel X550-AT chipset, delivering the power, performance and enhanced capabilities you need for dependable network connections. Compliant with IEEE 802.3u/ab/an standards, the 1-port 10G card delivers a dependable way to upgrade or replace your existing network port, providing throughput capability of up to 10Gbps in each direction (20Gbps total). It connects easily through a single, four-lane (x4 or higher) PCI Express slot.

The Intel X550-AT chipset provides many advanced features including Intel Virtualization Technology for connectivity and PXE network boot support. The Intel chipset provides many advanced features to support load-balancing the flow of network traffic, to enhance throughput and provide greater data reliability. It supports Audio-Video Bridging (AVB) to enable tightly controlled media stream synchronization, buffering and resource reservation. It also lets you take advantage of advanced features such as VLAN tagging, up to 15K jumbo frame support and Auto MDIX.

This five-speed NIC provides a cost-effective and versatile networking solution, by giving you the additional bandwidth your network needs without having to overhaul your infrastructure wiring. It lets you add an Ethernet port which can be accessed at multiple speeds 10G, 5G, 2.5G 1G and 100Mbps. Compatible with a broad range of operating systems, the 10G NIC is fully compliant with 10GBase-T and NBASE-T specifications. (10G network speeds require Cat6a cable. All other speeds require Cat5e cable.)

The PCIe 10G network card features advanced NBASE-T technology, supporting the latest multigigabit equipment, including new Cisco campus switches and Aruba Networks access points. The card enables you to connect to NBASE-T based equipment at network speeds of 2.5Gbps or 5Gbps, over your existing Cat5e infrastructure, without having to upgrade to more expensive Cat6a. The Ethernet network card also supports the more common 10G over copper, and 1G network connections using existing Cat 6/Cat5e or better cabling.

With its dual-profile design, the network card is easy to install into a wide range of computer/server chassis, regardless of form factor. The card comes equipped with a full-sized bracket, and includes a low-profile/half-height installation bracket that you can use as needed.

The ST10000SPEXI is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Upgrade your server or workstation to provide enhanced performance, advanced features and greater reliability
- Upgrade a 10/100/1000 Ethernet port on your computer to 10GbE networking
- Ideal for high-demand database servers and mission-critical systems that need redundant network connectivity
- Add networking capabilities to an old system with no Ethernet port

## Features

- Add a 10G /5G/2.5G/1G/100Mbps R-J45 Ethernet port to provide cost-effective network connectivity for high bandwidth workstations and servers
- Compliant with 10GBase-T and NBASE-T specifications
- Intel X550-AT chipset with Intel Virtualization Technology for connectivity (Intel VT-c)
- Fully compliant with IEEE 802.3an (10GBASE-T), IEEE 802.3ab (1GBASE-T), IEEE 802.3u (100BASE-T)
- Up to 20Gbps (full duplex) bandwidth
- Up to 9K jumbo frame support
- PXE network boot support and Auto MDIX

<b>Hardware</b>	Warranty	2 Years
	Ports	1
	Interface	RJ45 (10 Gigabit Ethernet)
	Bus Type	PCI Express
	Card Type	Standard Profile (LP bracket incl.)
	Port Style	Integrated on Card
	Industry Standards	IEEE 802.3an (10GBASE-T), IEEE 802.3ab (1GBASE-T), IEEE 802.3u (100BASE-T)
	Industry Standards	NBASE-T
	Industry Standards	IEEE 802.1Q VLAN Tagging
	Industry Standards	IEEE 802.3x Full Duplex Flow Control
	Chipset ID	PCI Express Rev 2.0

Intel - X550AT

<b>Performance</b>	Maximum Data Transfer Rate	10 Gbps
	Compatible Networks	10 Gbps/5G/2.5G/1G/100 Mbps
	Auto MDIX	Yes
	Full Duplex Support	Yes
	Jumbo Frame Support	9K max.
	Promiscuous Mode	Yes
	Supported Protocols	IEEE 802.3x (Flow Control Support)
		IEEE 802.1Q (VLAN tagging)
<b>Connector(s)</b>	Connector Type(s)	PCI Express x4
	Internal Ports	RJ-45
<b>Software</b>	OS Compatibility	Windows 7, 8, 8.1, 10
		Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019
		(Windows Drivers are supported in 64-bit only)
		Linux 2.4.x to 4.11.x <i>LTS Versions Only</i>
		ESXi 5.1/5.5/6.0
<b>Special Notes / Requirements</b>	System and Cable Requirements	For Windows, NBase-T support requires Windows 8 or higher
<b>Indicators</b>	LED Indicators	Link/Activity
	LED Indicators	10G/1G Speed
<b>Environmental</b>	Operating Temperature	5C to 50C (41F to 122F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	20~80%
<b>Physical Characteristics</b>	Color	Black
	Cable Length	3.9 in [100 mm]
	Product Length	6.0 in [1.5 cm]
	Product Width	2.7 in [68.500 mm]
	Product Height	4.8 in [1.2 cm]

	Weight of Product	3.4 oz [96.000 g]
<b>Packaging Information</b>	Package Length	8.2 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.6 in [40.000 mm]
	Shipping (Package) Weight	6.1 oz [172.000 g]
<b>What's in the Box</b>	Included in Package	10G network card
	Included in Package	low-profile bracket
	Included in Package	quick-start guide

***\*Product appearance and specifications are subject to change without notice.***

