

1-Port Gigabit PCIe Network Adapter Card, Low-Profile NIC, 10/100/1000Mbps PCI Express LAN Card, Realtek RTL8111H, Windows and Linux, TAA Compliant

Product ID: ST1000SPEX2LT



This TAA-compliant Gigabit Ethernet card adds a gigabit Ethernet interface to a desktop or server.


This 1-port network interface card is plug-and-play compatible, with drivers that auto-install on major operating systems such as Windows, Windows Server, and Linux. It is compatible with Intel and AMD hardware platforms equipped with PCI Express x1, x2, x4, x8, or x16 slots.

This network card features link speed and activity LED indicators for visual network speed verification and issue diagnosis.

This PCIe network adapter supports 9K jumbo frames to minimize packet overhead, Wake-on-LAN (WoL) for remote system booting, auto-negotiation between 10/100/1000Mbps, and VLANs for streamlined network management.

The PCI Express NIC includes a pre-installed low-profile bracket for compatibility with small form-factor computers, as well as a standard-profile bracket for full-sized desktops and servers.

Certifications, Reports and Compatibility



Applications

- Add an Ethernet port to a workstation or server computer, for redundancy or bridging

Features

- **TAA-COMPLIANT GIGABIT ETHERNET CARD:** Network Card with Realtek RTL8111H chip adds a gigabit ethernet interface to a desktop or server; Features link speed and activity LED indicators allowing users to visually diagnose issues and confirm network speeds
- **PLUG & PLAY COMPATIBILITY:** Network Interface Card drivers auto-install in most major operating systems including Windows, Windows Server, and Linux; Works with Intel and AMD hardware platforms that have a PCI Express x1, x2, x4, x8, or x16 slot
- **PERFORMANCE & MANAGEMENT:** PCIe Network Adapter Card supports 9K jumbo frames to reduce packet overhead, Wake-on-LAN (WoL) for remote system booting, auto-negotiation between 10/100/1000Mbps, and VLANs for efficient network management
- **UNIVERSAL FIT:** PCI Express NIC comes with a pre-installed low-profile bracket for small form-factor computers, and it includes a standard-profile bracket for compatibility with full-sized desktops and servers
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 1-port low-profile network card is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Ports	1
Bus Type	PCI Express
Card Type	Low Profile (SP bracket incl.)
Port Style	Integrated on Card
Industry Standards	IEEE 802.3
	IEEE 802.3u
	IEEE 802.3x
	IEEE 802.3ab
Chipset ID	Realtek - RTL8111H

Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	1000Mbps

Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
PXE	No
Jumbo Frame Support	9K max.
Promiscuous Mode	Yes

Connector(s)

External Ports	1 - RJ-45
Host Connectors	1 - PCI Express x1

Software

OS Compatibility	Windows 8/8.1, 10, 11 Windows Server 2016, 2019, 2022 Linux 2.4.x and up - LTS Versions only
------------------	--

Indicators

LED Indicators	1 - Right LED: Link/Activity Solid green: Active link Flashing green: Activity Off: No active link 1 - Left LED: Link Speed Solid green: 1Gbps link Solid orange: 10/100Mbps link
----------------	---

Power

Power Source	Bus Powered
--------------	-------------

Environmental

Operating Temperature	5C to 70C (41F to 158F)
Storage Temperature	0C to 80C (32F to 176F)
Humidity	10% ~ 80% (non-condensing)

Physical Characteristics

Color	Black
-------	-------

Product Length	2.6 in [6.5 cm]
Product Width	1.7 in [4.2 cm]
Product Height	0.7 in [1.8 cm]
Weight of Product	0.9 oz [26.0 g]

Packaging Information

Package Length	5.7 in [14.4 cm]
Package Width	6.9 in [17.4 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	3.2 oz [92.0 g]

What's in the Box

Included in Package	1 - PCIe Card
	1 - Full Profile Bracket
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***