

USB 3.0 to Dual DisplayPort Adapter, 4K 60Hz, DisplayLink Certified, USB to Dual DP Display Adapter, Dual DisplayPort Adapter for Mac & Windows

Product ID: USB32DP24K60



This USB to dual DisplayPort adapter lets you add two 4K 60Hz DisplayPort monitors to your Windows or Mac computer.

The adapter lets you use a single USB 3.0 port on your laptop to output dual 4K resolution at 60Hz to two independent displays. Simply plug the adapter into a USB 3.0 (5Gbps) port on your Windows or Mac system and connect your DisplayPort monitors to the adapter.

The adapter lets you enjoy the picture quality of Ultra HD video across multiple screens, even if your system doesn't natively support 4K video output.

With two UHD 4K displays, you can work more efficiently and accomplish more in the same amount of time. With each display delivering 4K performance, you can have four times the screen space compared to 1080p.

With multiple displays, you can output different content on each display at resolutions of up to 4096 x 2160p (60Hz). The dual DisplayPort adapter is ideal for business applications such as spreadsheets, word processors and web browsers. You can multitask and preview different data points across each display. For instance, you can calculate data on one display, write a report on the second display, and browse the internet on your laptops display.

The USB32DP24K60 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility







































Applications

- Connect two 4K displays to your computer system
- View large spreadsheets or several documents across multiple displays
- Increase productivity by running multiple applications on different displays; check your email on one display while editing a document on the other

Features

- CREATE A DUAL MONITOR WORKSTATION: Use this USB 3.2 5Gbps to Dual DisplayPort converter to connect your Windows or Mac laptop / desktop to two monitors, TVs or projectors using an available USB-A port; USB-powered, requiring no external power
- 4K RESOLUTIONS: With support for resolutions up to 4K 60Hz and widescreen capabilities this USB 3.2 external video & graphics card delivers a full UHD experience, ensuring astonishing picture quality; Enable extended display on Apple M1/M2/M3 MacBooks
- MULTI-USE FUNCTIONALITY: Use this IT-grade USB 3.2 Gen2 5Gbps display adapter to either extend or mirror your main laptop or desktop display onto two additional displays; Combine with USB31CAADP (sold separately) to connect to a USB-C host device
- NOTE: This adapter will not work with macOS version 10.13.4 to 10.13.6; We recommend users to update to 10.14 or later to ensure compatibility with DisplayLink; Driver required for macOS and Windows; Auto-driver install with ChromeOS
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this USB adapter is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty 2 Years

AV Input USB 3.2 Gen 1 (5Gbps)

Ports 2

AV Output DisplayPort

Audio Yes



USB Pass-Through No

Memory 2GB

Chipset ID DisplayLink - DL-6950

Performance

Maximum Digital Resolutions

Dual monitor: 4K @ 60 Hz

Supported Resolutions Widescreen(16/32 bit):

5120x2880 (using two DP ports), 4096x2160, 38402160, 2048x1152, 1920x1200, 1920x1080, 1680x1050, 1366x768,

1280x800, 1280x768, 1280x720

Standard(16/32 bit):

 $1600x1200,\,1400x1050,\,1280x1024,\,1024x768,\,800x600,\,$

640X480

Wide Screen Supported Yes

Audio Specifications 2-channel stereo

Connector(s)

Connector A 1 - USB Type-A (9 pin, 5 Gbps)

Connector B 2 - DisplayPort (20 pin)

Software

OS Compatibility Windows XP (32-bit), Vista, 7, 8, 8.1, 10, 11

macOS 10.6 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0

Ubuntu 18.04, 20.04, 22.04

Chrome OS v55+

Special Notes / Requirements

System and Cable

Requirements

System Processor: Quad Core 2.4GHz (i5 recommended)

System Memory: 4GB

Note This USB video adapter is not intended for graphical intensive

applications, such as gaming

Power





Power Source USB-Powered

Input Voltage 5V DC

Output Voltage 5 DC

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 70C (-4F to 158F)

Humidity 0~90% RH

Physical Characteristics

Color Black

Material Plastic

Cable Length 11.8 in [300 mm]

Product Length 6.1 in [15.5 cm]

Product Width 5.6 in [14.2 cm]

Product Height 1.2 in [3.0 cm]

Weight of Product 2.6 oz [73.0 g]

Packaging Information

Package Quantity 1

Package Length 6.8 in [17.2 cm]

Package Width 5.6 in [14.2 cm]

Package Height 1.3 in [3.2 cm]

Shipping (Package)

Weight

5.4 oz [154.0 g]

What's in the Box

Included in Package 1 - USB video adapter

1 - quick-start guide

^{*}Product appearance and specifications are subject to change without notice.