

USB 3.0 to HDMI / DVI External Video Card Multi Monitor Adapter – 1920x1080

Product ID: USB32HDE



The USB32HDE USB 3.0 to HDMI Adapter turns an available USB 3.0 port into an HDMI output, with high resolution 1920x1080 (1080p) video support - a convenient external video solution that makes it easy to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter functions as an external graphics card to deliver smooth, high-definition content to your HDMI or DVI-capable display (HDMI to DVI Adapter included). The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.
Recommended System Requirements:
CPU: Quad Core 2.4GHz or Higher (i5 recommended)
RAM: 4GB or higher

Certifications, Reports and Compatibility



Applications

- Add a secondary HDMI or DVI display and extend your desktop without taking apart your computer to install a new video card
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs, enabling connection to a secondary display/projector
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Use the adapter to connect your PC to your HDMI-equipped HDTV for viewing family pictures and movies
- Increase productivity by running multiple applications on different screens - check your email on one display and

search the web on the other

- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Supports resolutions up to 1920x1200
- Quick, easy installation
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation
- Supports the Windows Aero interface
- Supports 2-channel (Stereo) audio
- USB-powered - No external power adapter required
- SuperSpeed USB 3.0 (5 Gbps) Interface, backward compatible with USB 2.0
- Includes HDMI to DVI-D Adapter
- Supports the use of multiple USB32HDE adapters on a single system (up to 5)

Hardware	Warranty	2 Years
	AV Input	USB 3.0
	AV Output	HDMI
	Audio	Yes
	USB Pass-Through	No
	Memory	16MB
	Industry Standards	Standard HDMI, SuperSpeed USB 3.0, USB 2.0
	Chipset ID	Trigger - T5-302A

Performance	Maximum Digital Resolutions	1920x1200
	Supported Resolutions	Widescreen(16/32 bit):
	Wide Screen Supported	1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720
	Audio Specifications	
	General Specifications	Standard(16/32 bit):
		1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
		Yes
		2-Channel Stereo (48Khz)
		This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.

Connector(s)	Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	Connector B	HDMI (19 pin)
Software	OS Compatibility	Windows 10 (32/64)
		Windows 8 / 8.1 (32/64)
		Windows 7(32/64)
		Windows Vista (32/64)
		Windows XP (32/64)
Special Notes / Requirements	System and Cable Requirements	System Processor: Quad Core 2.4GHz (i5 recommended)
	Note	System Memory: 4GB
	Note	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic
	Note	Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources
		This USB video adapter is not intended for graphical intensive applications, such as gaming
Environmental	Operating Temperature	0C to 55C (32F to 131F)
	Storage Temperature	-10C to 75C (14F to 167F)
	Humidity	<85% RH Non-Condensing
Physical Characteristics	Color	Black
	Material	Plastic
	Cable Length	6.3 in [1.6 cm]
	Product Length	3.1 in [78 mm]
	Product Width	1.7 in [43.5 mm]
	Product Height	0.6 in [15.5 mm]
	Weight of Product	2.1 oz [60 g]
Packaging Information	Package Length	8.1 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.5 in [38 mm]
	Shipping (Package)	8.5 oz [240 g]

Weight

What's in the Box	Included in Package	USB 3.0 to HDMI Adapter
	Included in Package	Installation guide
	Included in Package	Driver CD
	Included in Package	HDMI to DVI-D Adapter

****Product appearance and specifications are subject to change without notice.***

