

USB 3.0 to VGA External Video Card Multi Monitor Adapter – 2048x1152

Product ID: USB32VGAE



The USB32VGAE USB 3.0 to VGA Adapter turns an available USB 3.0 port into a VGA output with support for high resolution video (up to 2048x1152) - a convenient external video solution that makes it easy to add multi-monitor/dual display capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0 connection, backward compatible with USB 2.0 connection).

Leveraging the high-bandwidth (up to 5 Gbps) SuperSpeed USB 3.0 interface, the adapter functions as an external graphics card to deliver smooth, high-resolution content to your VGA display; the adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

Backed by a StarTech.com 2-year warranty and free lifetime technical support. **Recommended System Requirements:**
CPU: Quad Core 2.4GHz or Higher (i5 recommended)
RAM: 4GB or higher

Certifications, Reports and Compatibility



Applications

- Add a secondary VGA display and extend your desktop without taking apart your computer to install a new video card
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs, enabling connection to a secondary display/projector
- Connect multiple VGA monitors to a single computer, to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and

search the web on the other

- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Supports resolutions up to 2048x1152
- Quick and easy installation
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation
- Supports the Windows Aero interface
- USB-powered - No external power adapter required
- SuperSpeed USB 3.0 (5 Gbps) Interface and backward compatible with USB 2.0

Hardware	Warranty	2 Years
	AV Input	USB 3.0
	AV Output	VGA
	USB Pass-Through	No
	Memory	16MB
	Industry Standards	SuperSpeed USB 3.0, USB 2.0
	Chipset ID	Trigger - T5-302A
Performance	Maximum Analog Resolutions	2048x1152
	Supported Resolutions	Widescreen(16/32 bit):
	Wide Screen Supported	2048x1152, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720
	General Specifications	Standard(16/32 bit):
		1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
		Yes
		This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.
Connector(s)	Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	Connector B	VGA (15 pin, High Density D-Sub)
Software	OS Compatibility	Windows 10 (32/64)
		Windows 8 / 8.1 (32/64)

Windows 7(32/64)

Windows Vista (32/64)

Windows XP (32/64)

Special Notes / Requirements	System and Cable Requirements	System Processor: Quad Core 2.4GHz (i5 recommended)
	Note	System Memory: 4GB
	Note	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic
	Note	Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources
		This USB video adapter is not intended for graphical intensive applications, such as gaming

Power	Power Source	USB-Powered
--------------	--------------	-------------

Environmental	Operating Temperature	0C to 55C (32F to 131F)
	Storage Temperature	-10C to 75C (14F to 167F)
	Humidity	<85% RH Non-Condensing

Physical Characteristics	Color	Black
	Material	Plastic
	Cable Length	6.3 in [1.6 cm]
	Product Length	3.1 in [78 mm]
	Product Width	1.7 in [43.5 mm]
	Product Height	0.6 in [15.5 mm]
	Weight of Product	10.6 oz [300 g]

Packaging Information	Package Length	8.1 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.5 in [38 mm]
	Shipping (Package) Weight	14.1 oz [400 g]

What's in the Box	Included in Package	USB 3.0 to VGA Adapter
--------------------------	---------------------	------------------------

Included in Package	Installation guide
Included in Package	Driver CD

****Product appearance and specifications are subject to change without notice.***

