

USB 3.0 Data Transfer Cable for Mac and Windows, 1,8m (6ft)

Product ID: USB3LINK



Here's an easy way to transfer files from your old computer to your new one. This data transfer cable lets you move files quickly over USB 3.0, and works with both Mac and Windows.

The transfer cable saves you time and effort when you're upgrading to a new computer. You can transfer your files and settings quickly over USB 3.0, also known as USB 3.1 Gen 1, with file transfer speeds up to 5 Gbps. Plus, there are no additional drivers to install when connecting your computers, because the necessary software is stored on the cable.

The data transfer cable supports a wide range of operating systems, working with Windows and Mac. The USB 3.0 transfer cable lets you transfer files between two computers including Windows to Windows, Windows to Mac, Mac to Windows, and even Mac to Mac.

The data transfer cable is compatible with Windows Easy Transfer software for migrating to newer versions of Windows, up to Windows 8. Plus, the built-in PCLinq software also allows file transfers in any direction between compatible operating systems, including Windows 10.

The USB3LINK data transfer cable comes in a convenient 2 m (6 ft.) length, and is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- When you upgrade to a new computer, transfer files and settings from your older PC or Mac
- An easy solution for transferring documents, photos, music and other files to your new computer
- Use it with Mac OSX 10.x, Mac OS X and Windows 7, 8, Vista and XP with no CD or download required

Features

- **EASY DATA TRANSFER:** This USB Data Transfer Cable connects directly over USB 3.0 (5Gbps) for file transfer and backup; Ideal for new system deployments, data migration or recovery applications
- **WIDE COMPATIBILITY:** Works with Windows and macOS; PCLInq software is stored on the cable and installs automatically when connected; No additional software or drivers required; Compatible with Windows Easy Transfer for system migration (up to Windows 8)
- **MAXIMUM PORTABILITY:** This 1,8 meter (6 foot) USB-A data transfer cable is USB bus-powered and does not require an external power adapter; Suitable for performing data transfers on-the-go
- **INCREASED PRODUCTIVITY:** USB 3.2 Gen 1 supports up to 5 Gbps speed and is backwards compatible with USB 2.0; Auto-driver setup enables convenient data transfer to multiple workstations with minimal setup time
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB A Data Transfer Cable is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Ports	1
Chipset ID	Prolific - PL27A1

Performance

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
MTBF	500,000

Connector(s)

Connector Type(s)	1 - USB Type-A (9 pin, 5 Gbps)
-------------------	--------------------------------

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 11
------------------	--------------------------------------

macOS 10.7.5 to 10.15

Note: The provided PCLinq software is required in Windows 10, 8.1, and macOS. In Windows 10 and 8.1, Microsoft removed support for cables from the Windows Easy Transfer software.

Indicators

LED Indicators	2 - Link/Activity
----------------	-------------------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5%RH ~ 85%RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	6.0 ft [1.8 m]
Product Width	0.9 in [2.4 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	2.8 oz [80.0 g]

Packaging Information

Package Quantity	1
Package Length	6.4 in [16.2 cm]
Package Width	5.2 in [13.3 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	4.4 oz [126.0 g]

What's in the Box

Included in Package	1 - USB 3.0 Transfer Cable
---------------------	----------------------------

1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***