

2 Port VGA Video Splitter - 2 Monitore - 1 x VGA (Stecker) 2 x VGA (Buchse)

Produkt-ID: ST122PRO



The ST122PRO 2 Port High Resolution VGA Video Splitter - 350 MHz splits a VGA video source signal to 2 monitors or projectors simultaneously - a professional grade solution that is perfect for presentations, classrooms, tradeshow, or in-store displays, where the highest-quality identical video output on several monitors is needed.

This High Resolution VGA Splitter supports monitors with up to 350MHz of video bandwidth and display resolutions up to 2048x1536 @80Hz. For added versatility, the VGA splitter features an integrated booster circuit that allows the video signal to be extended up to 210 feet (65 meters), enabling you to situate your displays in the most convenient location based on your application.

This product is TAA compliant., Male to Female VGA extension cable required (MXT101HQ)

Zertifikate Berichte und Kompatibilität



Anwendungen

- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Display travel schedules and alerts in airports, bus terminals and train stations etc.
- Create eye-catching displays in trade-shows and auditoriums

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Merkmale

- Allows 1 VGA video source to simultaneously duplicate to 2 different monitors
- Supports resolutions up to 2048x1536 @ 80Hz; High video bandwidth (350 MHz)
- Daisy chainable to mirrored output for almost unlimited expansion
- Integrierter Videoverstärker verstärkt das Signal für eine Kabellänge von bis zu 65 m.
- Uses standard monitor extension cables; DDC compatible; Includes AC 120V power adapter

Hardware

Garantiebestimmungen	2 Years
Ports	2
Audio	Nein
Behördliche Genehmigungen	FCC Part 15 Class A, CE Mark
Industrienormen	DDC compatible - all other monitors must be able to support the highest video resolution of the DDC-type monitor connected to Video Out 1

Leistung

Max. Kabellänge	213.2 ft [65 m]
Max. Analogauflösungen	2048x1536 @ 80Hz
Bandbreite	(-3db): 350 MHz
Allgemeine Spezifikationen	Male to Female VGA extension cable required (MXT101HQ)
MTBF	1,588,136 Hours

Steckverbinder

Steckverbindertyp(en)	2 - VGA (15-polig, High Density D-Sub)
	1 - VGA (15-polig, High Density D-Sub)

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	0.3 A
Ausgangsspannung	5 DC
Ausgangsstrom	1 A
Steckertyp	N
Stromverbrauch	5

Umgebungsbedingungen

Betriebstemperatur	0 to 40 °C
Lagertemperatur	5 to 40 °C
Feuchtigkeit	0~80% RH Non-condensing

Physische Eigenschaften

Farbe	Schwarz
Gehäusotyp	Stahl
Produktlänge	7.1 in [18.0 cm]
Produktbreite	3.1 in [8.0 cm]
Produkthöhe	0.8 in [2.1 cm]
Produktgewicht	12.9 oz [366.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.4 in [18.7 cm]

Paketbreite 9.4 in [24.0 cm]

Pakethöhe 3.8 in [9.7 cm]

Versandgewicht
(Verpackung) 1.4 lb [0.7 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 2 Port High Res. Video Splitter
	4 - Rubber feet
	1 - Power Adapter
	1 - Instruction Manual

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.