

4 Port High Resolution 350 MHz Video Splitter

Product ID: ST124PROEU



The ST124PROEU 4 Port High Resolution VGA Video Splitter - 350 MHz splits a VGA video source signal to 4 monitors or projectors simultaneously - a professional grade solution that is perfect for presentations, classrooms, tradeshows, or in-store displays, where the highest quality video on several monitors is needed.

This High Resolution VGA Splitter supports monitors with up to 350MHz of video bandwidth and display resolutions up to 2048x1536 @80Hz. For added versatility, the VGA splitter features an integrated booster circuit that allows the video signal to be extended up to 210 feet (65 meters), enabling you to situate your displays in the most convenient location based on your application.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support. Male to Female VGA extension cable required (MXT101HQ)

Certifications, Reports and Compatibility



Applications

- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Display travel schedules and alerts in airports, bus terminals and train stations etc.
- Create eye-catching displays in trade-shows and auditoriums
- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Allows 1 VGA video source to simultaneously display on 4 different monitors
- Supports resolutions up to 2048x1536 @ 80Hz
- High video bandwidth (350 MHz)
- Daisy chainable for almost unlimited expansion
- Maximum VGA cable length of 210ft (65m)
- Uses standard monitor extension cables (See Accessories)
- DDC compatible

Hardware	Warranty	2 Years
	Ports	4
	Industry Standards	DDC compatible - all other monitors must be able to support the highest video resolution of the DDC-type monitor connected to Video Out 1
Performance	Maximum Cable Length	213.2 ft [65 m]
	Maximum Analog Resolutions	2048x1536 @ 80Hz
	Bandwidth	(-3db) 350MHz
	General Specifications	Male to Female VGA extension cable required (MXT101HQ)
Connector(s)	Connector Type(s)	VGA (15 pin, High Density D-Sub)
	Connector Type(s)	VGA (15 pin, High Density D-Sub)
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.4A
	Output Voltage	5 DC
	Output Current	2A
	Center Tip Polarity	Positive
	Plug Type	N
	Plug Type	N
	Power Consumption (In Watts)	10
Environmental	Operating Temperature	5C to 40C (41F to 104F)
	Humidity	0~80% RH
Physical Characteristics	Color	Black
	Material	Steel

Product Length	7.2 in [1.8 cm]
Product Width	3.3 in [85 mm]
Product Height	0.8 in [20 mm]
Weight of Product	14.1 oz [400 g]

Packaging Information	Package Length	9.4 in [2.4 cm]
	Package Width	7.2 in [1.8 cm]
	Package Height	3.6 in [92 mm]
	Shipping (Package) Weight	24.7 oz [700 g]

What's in the Box	Included in Package	4 Port High Res. Video Splitter
	Included in Package	Rubber Feet
	Included in Package	Power Adapter
	Included in Package	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

