2-Post 6U Wall Mount Rack, Adjustable Depth up to 16in (40cm), Bracket for 19-inch Server/Data/Networking Equipment, Open Frame, Max 88lb (40kg)

Product ID: WALLMOUNT6-HAF



This 2-post 6U adjustable wall mount bracket provides a convenient solution for mounting 19-inch rack-mountable shallow servers, patch panels, NAS devices, UPS, data, and networking equipment. The adjustable depth enables customization to accommodate various equipment sizes.

This wall-mount rack features fold-out sides for quick setup, ships fully assembled flat-packed, and includes all the necessary hardware: wood stud screws, M5 cage nuts, and M5 screws and speed up deployment. Four keyhole wall mounting holes provide a straightforward way to securely mount or unmount the rack. The mounting holes are spaced 16" (40.6cm) to match existing wall-stud framework.

The 2-post open rack features an adjustable depth range from 9.6 to 15.6in (24.5 to 39.7cm) to accommodate larger rack-mountable devices. The additional depth can also be used for equipment that may require additional clearance at the back for cable management.

Wall-mount rack bracket is made from 14-gauge (2mm) SPCC steel that can support up to 88lb (40kg) of equipment, providing a stable and sturdy mounting point. The powder-coated finish ensures long-lasting durability, protecting the rack from wear and tear.

Certifications, Reports and Compatibility

Applications

Features

• 6U WALL MOUNT ADJUSTABLE RACK: 2-Post 6U wallmount rack supports 19-inch shallow server racks, shelves, patch panels, UPS, data, and networking equipment; Adjustable mounting depth up to 15.6in (39.7cm) deep; EIA-310-compliant

• READY TO USE: Wall-mount rack features fold-out sides for quick setup, ships fully assembled flat-packed, and includes wood stud screws, M5 cage nuts, and M5 screws; Four keyhole mounting holes ensure easy installation and removal

• ADJUSTABLE DEPTH: Customize the mounting depth from 9.6 to 15.6in (24.5 to 39.7cm) to accommodate different sized equipment; The side panels feature handles and preset adjustment holes for easy depth customization

• WEIGHT CAPACITY AND MOUNTING: This wall bracket can hold up to 88lb (40kg), providing a reliable solution for equipment mounting; Wall mounting holes are spaced 16" (40.6cm) apart enabling secure anchoring to existing construction framework

• DURABLE STEEL CONSTRUCTION: Built from 14-gauge (2mm) solid steel with a powder-coated finish, this open-frame rack delivers exceptional strength and durability for long-term mounting; Wall mount bracket is backed for life and 24/5 technical assistance

General		
	UPC	065030912860
	Warranty	Lifetime
Physical & Environmental		
	Color	Black
	Construction Material	Steel
	Product Length	20.1 in [51 cm]
	Product Width	11.8 in [30 cm]
	Product Height	1.3 in [33 mm]
	Weight of Product	14.5 lb [6.6 kg]
	Maximum Mounting Depth	15.7 in [39.8 cm]
	Minimum Mounting Depth	9.7 in [24.5 cm]
Performance		
	Weight Capacity (No Casters)	88.2 lb [40 kg]
Hardware		

	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	6U
	Special Features	Ships Fully Assembled
		Wall-Mountable
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Packaging & In-the-Box		
	Included in Package	1 - 6U Wall Mount Rack
		12 - M5x15 Screws
		12 - M5 Cage Nuts
		4 - M8x50 Screws
		4 - M6x12 Screws
		1 - Quick-Start Guide
	Flat Pack (Assembly Required)	Yes
	Package Width	22.2 in [56.5 cm]
	Package Depth	14.8 in [37.5 cm]
	Package Height	3.9 in [100 mm]
	Shipping (Package) Weight	16.1 lb [7.3 kg]

Product appearance and specifications are subject to change without notice.