

Bulk Cat 6 Ethernet Cable - 1000 ft. - Solid - CMP/FT6 Plenum Fire Rating - ETL Verified  
- Gray - TAA Compliant

Produkt-ID: WIRC6CMPGRY



The WIRC6CMPGRY Cat6 Plenum Bulk Cable (1000 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a foot-marked jacket that enables you to measure your cable runs to your exact installation requirements. Also, the gray PVC jacket enables you to color code your drops as needed for a more organized installation.

Constructed of only top quality materials, the WIRC6CMPGRY delivers reliable performance and is backed by our Lifetime Warranty.

This Category 6 cable has been tested for CMP (FT6) plenum-ratings, and is ideal for installation in air plenums, ducts, walls, conduit, ceilings, etc. where CMP fire rating is required.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 23 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Our Bulk network cables are ETL Verified to meet ANSI/TIA-568.2-D standards, ensuring peak performance for high-speed applications. Independent testing confirms compliance with strict insertion loss, return loss, and crosstalk limits, maintaining stable signal transmission over longer runs.

Zertifikate Berichte und Kompatibilität



## Anwendungen

- Can be used in air ducts and plenums where CMP fire rating is required
- Designed for use with Gigabit networks

## Merkmale

- CAT6 ETHERNET CABLE: 1000 ft. Solid UTP Cat6 cable optimized for enterprise 10 Gigabit networks; 550 MHz frequency enhances throughput; Supports Power over Ethernet (PoE) and 4K or 1080p video streaming; ETL Verified to meet ANSI/TIA-568.2-D standards
- Längen-markiertes Kabel
- ETL-verifiziert
- APPLICATIONS: Ideal for installations (air plenums, ducts, walls, conduits, ceilings, etc.) where air circulates in buildings and CMP/FT6 Plenum products are required
- Sorgfältig entwickelt und getestet für akzeptable Nah-Nebensprechen-Werte (Near End Crosstalk - NEXT)

---

### Hardware

Garantiebestimmungen Lifetime

Typ der Kabelummantelung PVC - Polyvinyl Chloride

Feuerwiderstandssklasse Ausgelegt gemäß CMP (Plenum)  
e

---

### Leistung

ETL-verifiziert Ja

Kabelnennwerte CAT6 - 500 MHz

---

### Physische Eigenschaften

Farbe Grau

|                |                     |
|----------------|---------------------|
| Drahtstärke    | 23 AWG              |
| Leitungstyp    | Massives Kupfer     |
| Kabellänge     | 1000.0 ft [304.9 m] |
| Produktlänge   | 1000.0 ft [304.9 m] |
| Produktbreite  | 0.2 in [0.5 cm]     |
| Produkthöhe    | 0.2 in [0.5 cm]     |
| Produktgewicht | 30.0 lb [13.6 kg]   |

---

#### Verpackungsinformationen

|                             |                   |
|-----------------------------|-------------------|
| Paketmenge                  | 1                 |
| Paketlänge                  | 17.0 in [43.1 cm] |
| Paketbreite                 | 9.3 in [23.5 cm]  |
| Pakethöhe                   | 17.2 in [43.8 cm] |
| Versandgewicht (Verpackung) | 33.7 lb [15.3 kg] |

---

#### Verpackungsinhalt

|                    |                                                                |
|--------------------|----------------------------------------------------------------|
| Im Paket enthalten | 1 - 1000 ft Roll of Gray Plenum CMP Cat 6 Solid UTP Bulk Cable |
|--------------------|----------------------------------------------------------------|

---

#### Garantieinformationen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.