

4 User 16 Port Cat5 Matrix IP KVM Switch

Produkt ID: SV1654DX4I



The SV1654DX4I 4-User 16-Port Enterprise class CAT 5 Matrix IP KVM Switch provides multi-user control of connected servers, devices and services connected through a local network infrastructure. Allowing a total of 4 independent user channels at any time, you have the freedom to choose a combination of IP users, local user and on-site remote console user (using a console extender device – SV5CONS not included) to access up to 4 connected systems simultaneously.

The IP KVM switch allows users to reboot the system, access the BIOS, install applications or operating systems, transfer files over virtual media, and have full control over the keyboard and mouse as if they are on site, saving time and resources by providing complete remote control of connected equipment.

Aside from a dependable and convenient operating platform, the matrix switch also provides features essential for secure and efficient management of mission-critical servers and devices - day in and day out.

How it works:

Connectivity Diagram

Note: The following interface modules are required for host connectivity

SV5USBM - USB Server Interface Module for the Enterprise Series IP KVMs

SV5PS2M - PS/2 Server Interface Module for the Enterprise Series IP KVMs

Certifikat, rapporter och kompatibilitet

Användning

- Users can reboot the system, access the BIOS, and have full control over the keyboard and mouse - as if they are on site
- Administer multiple servers for your Co-Location/ISP facility at the BIOS level either onsite or remotely saving time and money
- Create a scalable, streamlined access solution in your Datacenter or Server Farm
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Scale existing infrastructure, and access existing KVM analog switches via TCP/IP
- Remote access for outsourced server / IT hardware management, saving travel time
- Remote access to mission-critical corporate datacenter servers ensuring maximum uptime

Funktioner

- BIOS level control of the attached servers from anywhere over the internet
- 4 connected channels at a time from: 4 IP users, 1 local user, and 1 remote console extender user
- Supports virtual media and file transferring for connected servers (with the use of the USB 2.0 Interface Modules)
- Local hard drive can be connected to the KVM and used as a shared resource among all connected servers without affecting regular network traffic to file servers
- Longest supported distance from the server to the KVM compared to competitors (164 feet)
- Serial control via SSH and Telnet through the IP interface
- Secure access to the web console via user ID and SSL password
- Supports up to 32 user accounts and incorporates SSL encryption of session data, and SSL web communication encryption
- High resolution support for 1600 x 1200 @ 75Hz
- Supports a maximum resolution of 1600 x 1200 at 16 bit via the web interface
- Low Power consumption (as much as 25% lower than competitors)
- Versatile wide range power support, works with anything from 85-260 VAC

- Crash Cart ports on the front of the KVM for quick connections
- Plug and Play compliant hybrid KVM supporting both USB and PS2
- Web interface works with smartphone devices that support VNC or Java, for control while mobile
- Works with PC, Mac, Linux and Sun Systems
- Upgradeable firmware
- Each computer name can be defined via the OSD menu and Web interface
- Obtains an IP address using DHCP or manual configuration
- Made in North America

Hårdvara

Garantipolicy	2 Years
Audio	Nej
KVM-portar	16
PC-gränssnitt	USB och PS/2
PC-videotyp	VGA
Flera skärmar	1
Hyllmonterbar	Ja
Medföljande kablar	Nej
Kedjekoppling	Nej

Prestanda

IP-kontroll	Ja
Hot-Key Selection	Ja
Maximal analog upplösning	Standard(4:3) - 1600x1200 @60Hz (Recommended 1280x1024) Widescreen(16:9) - 1280x960
Maximalt antal användare	1 x Local, 1 x Remote Console, 4 x IP User - Total 4

Stöd för portval	Genvägskommandon och OSD (visning på skärmen)
Säkerhetsfunktioner	128-bit SSL-kryptering
Stödda protokoll	SSH, HTTP, SNMP, HTTPS, VNC VNCS, Radius

Kontakt(er)

Konsolgränssnitt	PS/2 (6-stifts, Mini-DIN)
	RJ-45
	RJ-45
	RJ-45
	USB Type-A (4-stifts) USB 2.0
	VGA (15-stifts, High Density D-Sub)
Värdkontakter	RJ-45

Särskilda anmärkningar/krav

Obs.	<p><p>Source code for the unit operating system is available upon request. Please contact us by phone, live chat, or email to make your request. </p><p>This offer is valid for three years from the date of purchase and/or for as long as parts or customer support is offered for this product.</p><p>Charges for the reasonable cost of copying and/or conveying may apply.</p></p>
------	---

Indikatorer

LED-indikatorer	Link
	Power

Ström

Power Source	AC-adapter medföljer
Inspänning	115V-230V AC

Miljö

Drifttemperatur	0 - 40°C (32 - 104°F)
Förvaringstemperatur	-40 - 65°C (-40 - 158°F)

Luftfuktighet 80% RHNC

Utseende

Färg	Svart
Kabinetttyp	Stål
Produktbredd	17.3 in [44 cm]
Produkt höjd	1.7 in [44 mm]
Produkt djup	12.2 in [31 cm]
Produkt vikt	4.9 lb [2.2 kg]

Förpackning

Package Length	22.6 in [57.4 cm]
Package Width	4.1 in [10.5 cm]
Package Height	14.7 in [37.4 cm]
Fraktvikt (förpackning)	6.6 lb [3.0 kg]

Vad det är i lådan

Ingår i paketet	16 Port IP KVM
	Rack Mounting Hardware
	Power Cable
	Manual on Cd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

