

2 Port USB 2.0 Extender Hub over Cat5e/Cat6 Cable (RJ45) - 330ft/100m Industrial Metal USB Extender Adapter Kit w/ ESD Protection - Externally Powered - 480 Mbps

Produkt-ID: USB2002EXT2NA



The USB2002EXTNA USB 2.0 extender over ethernet lets you extend a USB 2.0 connection over distances of up to 100-meters (330-feet), over standard Cat5e or Cat6 ethernet LAN cabling.

With data bandwidth of up to 480 Mbps and no software installation required, the USB extender over Cat5e, Cat6, or Cat7 offers a fast, easy, and versatile solution for business or industrial applications with durable metal housing, an included surface-mounting bracket kit and simple plug-and-play installation.

Plus, the 100m USB extender provides up to the full 500 mA of power (with the use of an external power adapter at the local or remote end) allowing for greater compatibility with bus-powered USB devices.

Connecting older peripherals isn't a problem. This versatile USB over network extender is backward compatible with legacy USB 1.0 devices. The USB over ethernet hub enables almost any kind of USB device to be placed at remote locations away from the host computer.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales

The USB2002EXT2NA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **USB 2.0 EXTENDER:** Connect 2 USB devices up to 330ft/100m over CAT5e/CAT6 RJ45 ethernet network cable w/ data transfer rates up to 480Mbps; Status LEDs for power, activity, link & host connectivity; Newer version of our extender USB2002EXT2
- **CONNECT REMOTE USB DEVICES:** The USB extender creates a 2 port hub to remotely access USB devices like printers, cameras, plotters, keyboard/mouse, displays, & CCTV systems at a convenient location
- Entspricht den Hochgeschwindigkeits-USB 2.0-Spezifikationen mit Unterstützung für Datenübertragungsraten von bis zu 480 Mbit/s
- Bis zu 500 mA pro Port für USB-betriebene Geräte
- **PLUG-AND-PLAY:** The multi sub extender features driverless installation & is compatible w/ major operating systems incl. Windows, macOS, Linux; Backwards Compatible with USB 1.0 and USB 1.1 devices

Hardware

Garantiebestimmungen 2 Years

Ports 2

Kabel Cat5 UTP

Leistung

Max. Datenübertragungsrate 480 Mbps

Max. Entfernung 100m [328ft]

Steckverbinder

Anschlüsse lokales 1 - USB B (4-polig)

Gerät		1 - RJ-45
	Remote-Gerät-Anschlüsse	2 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
		1 - RJ-45
Software		
	Betriebssystemkompatibilität	OS Independent; No additional drivers or software required
Spezielle Hinweise/Anforderungen		
	System- und Kabelanforderungen	USB enabled computer system with available USB port
Strom		
	Stromversorgung	Mit Netzadapter
	Eingangsspannung	100 - 240 AC
	Eingangsstrom	0.58 A
	Ausgangsspannung	24 DC
	Ausgangsstrom	1.0 A
	Polarität der Mittelspitze	Positiv
	Steckertyp	M
	Stromverbrauch	24
Umgebungsbedingungen		
	Betriebstemperatur	0°C to 50°C (32°F to 122°F)
	Lagertemperatur	-20°C to 70°C (-4°F to 158°F)
	Feuchtigkeit	10~90% RH
Physische Eigenschaften		

Farbe	Schwarz
Gehäusotyp	Aluminium und Kunststoff
Produktlänge	3.4 in [8.7 cm]
Produktbreite	3.0 in [7.6 cm]
Produkthöhe	1.0 in [2.6 cm]
Produktgewicht	10.2 oz [289.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.6 in [24.3 cm]
Paketbreite	7.8 in [19.8 cm]
Pakethöhe	3.1 in [7.9 cm]
Versandgewicht (Verpackung)	1.8 lb [0.8 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Lokales Gerät
	1 - Remote-Gerät
	1 - Montageset
	1 - Universales Netzteil
	1 - 6 ft [180 cm] North America Power Cord
	1 - USB-Kabel
	1 - Kurzanleitung

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.