

## USB 2.0 to eSATA Adapter

**Product ID:** USB2ESATA



This USB 2.0 to external SATA Adapter allows you to connect a SATA or eSATA drive to your computer through an available USB 2.0 port - essentially converting the USB port to an external Serial ATA port.

Ideal for 2.5in or 3.5in optical drives and eSATA enclosures, this convenient adapter offers a cost-effective solution that lets you quickly connect Serial ATA based devices for testing and transferring files without having to open the computer chassis.

## Certifications, Reports and Compatibility

### Applications

- Connect SATA drives to a computer without having to install internally or into an enclosure
- Technicians who need to regularly connect different SATA hard drives quickly

### Features

- Standard eSATA external interface
  - High Speed USB 2.0 compliant host interface which supports transfer rates up to 480 Mbps
  - 48-bit LBA support
  - No driver/software installation required
-

## Hardware

Warranty	2 Years
Interface	eSATA
Bus Type	USB 2.0

---

## Performance

Maximum Data Transfer Rate	USB 2.0: 480 Mbps
LBA support	48-bit

---

## Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0
External Ports	eSATA (7 pin, Data)

---

## Software

OS Compatibility	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, Mac OS X and higher
------------------	---

---

## Special Notes / Requirements

System and Cable Requirements	Available USB 2.0 port
-------------------------------	------------------------

---

## Power

Power Source	Not Included (not required for standard applications)
--------------	---

---

## Physical Characteristics

Color	Black
-------	-------


---

## Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	1.3 in [33 mm]
Package Height	6.5 in [16.5 cm]
Shipping (Package) Weight	5.3 oz [150 g]

---

## What's in the Box



Included in Package	USB to eSATA Adapter
	Driver CD
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

