

USB to 3.4mm Power Cable - Type H Barrel - 3 ft

Produkt ID: USB2TYPEH



Tired of having to carry around a separate wall adapter in order to power or charge your 5V devices, such as certain external hard drives, streaming media players, and Bluetooth® speakers?

This USB power cable makes it easier to power 5V DC devices that have a Type H (OD: 3.4mm, ID: 1.3mm) barrel power connector. You can power or charge the devices through an available USB port on your laptop or desktop computer.

Expertly designed and constructed of high-quality materials, the StarTech.com USB2TYPEH power cable is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Power your external hard drive or other devices that are equipped with a Type-H power connector through an available USB port on your computer
- Charge your Bluetooth speakers and other chargeable devices through an available USB port on your computer

Funktioner

- Molded connectors with strain relief
- Aluminum-mylar foil with braided shielding

- Durable PVC construction

Hårdvara

Garantipolicy	1 Year
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	USB Type-A (4-stifts) USB 2.0
Connector B	Cylindrisk strömkontakt (storlek H, OD: 3,40, ID: 1,30)

Ström

Polaritet på mittpol	Positiv
Kontakttyp	H

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-10°C to 30°C (14°F to 86°F)
Luftfuktighet	30%-75% RH

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	36.0 in [91.4 cm]
Produktlängd	36.0 in [91.4 cm]
Produktbredd	0.6 in [15.0 mm]
Produkt höjd	0.3 in [8.0 mm]
Produktvikt	0.9 oz [26.0 g]

Förpackning

Förpackningsantal	1
-------------------	---

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Fraktvikt (förpackning)	1.1 oz [32.0 g]

Vad det är i
lådan

Ingår i paketet	3 ft USB to Type H Barrel 5V DC Power Cable
-----------------	---

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

