

USB 3.0 to VGA External Multi Monitor Graphics Adapter with 3-Port USB Hub – VGA and USB 3.0 Mini Dock – 1920x1200 / 1080p

Product ID: USB32VGAEH3



The USB32VGAEH3 USB 3.0 to VGA Adapter turns a USB 3.0 port into a VGA output port with 1920x1200/1080p video support. The adapter features a built-in 3-port USB 3.0 hub, which enables you to connect three different USB devices, along with the display adapter, to the same USB 3.0 port – an ideal workaround for Ultrabook or laptop computers that have a limited number of USB ports available.

Functioning as an external graphics card, this USB to VGA adapter provides a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer. Leveraging the high-bandwidth (5 Gbps) USB 3.0 interface, the adapter delivers smooth, high-definition content to your VGA monitor / projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

The USB32VGAEH3 also features a built-in 3-port USB 3.0 hub, which lets you use the device as a mini dock for connecting peripherals such as a mouse, printer and keyboard along with your monitor. Then, it's as easy as connecting your laptop to the adapter to sync each device at your work station – a versatile solution for making your laptop portable when you want it to be, and powerful when you need it to be.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Recommended System Requirements:
CPU: Quad Core 2.4GHz or Higher (i5 recommended)
RAM: 4GB or higher
Available USB 3.0 port

Certifications, Reports and Compatibility

Applications

- Add a secondary VGA display and extend your desktop

- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Run multiple applications on different screens - check your email on one display and search the web on the other
- Simultaneously view large or multiple spreadsheets across several displays
- Connect your PC to your VGA-equipped projector or display for viewing family pictures and movies
- Great for boosting productivity for researchers and writers, offering the ability to have reference material on one display and a working document copy on the other
- Add an extra VGA display and 3 additional USB devices to an Ultrabook or laptop computer with limited USB and video output ports

Features


- High-bandwidth USB 3.0 host connection, for reliable high-definition video playback
- Built in 3-Port USB 3.0 hub offers improved connectivity options on your slimline laptop or Ultrabook
- USB 3.0 (5 Gbps) Interface, backward compatible with USB 2.0
- Fast, easy installation
- USB-powered - No external power adapter required
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation

Hardware

Warranty	2 Years
AV Input	USB 3.0
AV Output	VGA
Audio	No
USB Pass-Through	Yes
Memory	16MB
Industry Standards	SuperSpeed USB 3.0, USB 2.0
Chipset ID	Trigger - T5-302

Performance

Maximum Analog	1920x1200
----------------	-----------



Resolutions

Supported Resolutions	<p>Widescreen(16/32 bit):</p> <p>1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720</p> <p>Standard(16/32 bit):</p> <p>1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600</p>
Wide Screen Supported	Yes
General Specifications	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	VGA (15 pin, High Density D-Sub)
	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility	<p>Windows 10 (32/64)</p> <p>Windows 8 / 8.1 (32/64)</p> <p>Windows 7(32/64)</p> <p>Windows Vista (32/64)</p> <p>Windows XP (32/64)</p>
Microsoft WHQL Certified	Yes

Special Notes / Requirements

System and Cable Requirements	<p>System Processor: Quad Core 2.4GHz (i5 recommended)</p> <p>System Memory: 4GB</p>
Note	<p>This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic</p> <p>Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system</p>



resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-10C to 75C (14F to 167F)
Humidity	< 85% non-condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	6.0 in [15.2 cm]
Product Length	9.3 in [23.5 cm]
Product Width	1.7 in [44 mm]
Product Height	0.6 in [14 mm]
Weight of Product	7.5 oz [212 g]

Packaging Information

Package Length	8.3 in [21 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.5 in [38 mm]
Shipping (Package) Weight	7.5 oz [212 g]

What's in the Box

Included in Package	USB 3.0 to VGA Adapter w/ 3-Port USB 3.0 Hub
	Instruction Manual
	Software Installation Disc



****Product appearance and specifications are subject to change without notice.***

