

HDMI to USB-C Video Capture Device - 1080p 60fps

Product ID: USBC2HDCAPRO



This HDMI to USB-C video capture device works as an external USB capture card to record high-definition HDMI video to your USB-C, USB-A or Thunderbolt 3 computer. With an aluminum enclosure, this device is built strong for fixed-location or on-the-go capture. It offers a separate 3.5 mm audio input for accompanying audio or voice-overs, and an HDMI pass-through port for connecting a monitor to review the video as it's captured.

The included software makes USB-C HDMI capture easy by turning your computer into an HDMI recorder. Using a widely adopted codec, videos saved in StreamCatcher work with almost any video player and require no converting or editing.

On Windows, you can live broadcast your video over the internet, using Twitch or other third-party video streaming platforms, with the included software.

With this HDMI to USB video capture device, you can record meetings, presentations, conference calls and security footage, saving 1080p HD video at 60fps directly to your computer for easy editing and sharing.

With this HDMI to USB 3.0 video capture device, you can record raw/lossless video using any third-party DirectShow compatible software, such as Open Broadcaster Software (OBS).

The USBC2HDCAPRO is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Record video for training and tutorial purposes
- Capture live video by connecting the camera directly to the device

- Live stream the connected video source over the internet

Features

- Hassle-free video recording with intuitive software included for Windows and macOS
- Seamless picture quality with USB 3.0 bandwidth enabling you to capture 1080p video at 60fps
- Platform freedom with DirectShow compatibility enabling you to use your preferred software

Hardware

Warranty	2 Years
AV Input	HDMI
AV Output	USB
Audio	Yes
Industry Standards	NTSC, PAL-M, PAL-60, PA
	Video Encoding: MPEG4/H.264
	DirectShow Compatible
Chipset ID	Mstar - MST3363CNK-170

Performance

Maximum Digital Resolutions	1920 x 1080 60 FPS
Supported Resolutions	1920 x 1080, 1280 x 720, 1024 x 768, 800 x 600
Wide Screen Supported	Yes
Audio Specifications	2-channel stereo audio
MTBF	3,104,896 Hours

Connector(s)

Connector A	HDMI (19 pin)
	3.5 mm Mini-Jack (3 Position)
Connector B	USB Type-B (9 pin) USB 3.0

Software



OS Compatibility	Windows 7, 8, 8.1, 10, 11 MacOS 10.11 to 10.14
------------------	---

Special Notes / Requirements

Note	This video capture device requires a USB 3.0 port (or higher). The video capture device does not work with USB 2.0 ports (or lower). The capture software included for macOS does not support video streaming
------	--

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-5C to 40C (23F to 105F)
Humidity	20% to 80% (non-condensing)

Physical Characteristics

Product Length	3.6 in [92 mm]
Product Width	2.3 in [58 mm]
Product Height	1.1 in [28 mm]
Weight of Product	3.1 oz [88 g]

Packaging Information

Package Length	6.0 in [15.2 cm]
Package Width	8.5 in [21.5 cm]
Package Height	2.1 in [53 mm]
Shipping (Package) Weight	11.8 oz [334 g]

What's in the Box

Included in Package	USB-C capture device 6ft [2m] USB-C to USB-B cable
---------------------	---



3.3 ft [1 m] USB-A to USB-B cable

3.3 ft [1 m] HDMI cable

****Product appearance and specifications are subject to change without notice.***

