

1:7 Standalone USB Duplicator and Eraser - for USB Flash Drives

Product ID: USBDUPE17



This USB duplicator and eraser lets you clone or erase up to seven USB flash drives, without a host computer connection. This means you can work more efficiently and manage larger batches of USB drives, saving time and effort.

The standalone USB duplicator and eraser is perfect for IT professionals and system administrators in corporate, education, marketing, or sales environments.

The duplicator lets you copy up to seven drives simultaneously, and offers both synchronous and asynchronous duplication, with speeds up to 1.5GB per minute. The asynchronous feature means you can remove and replace USB storage devices while other copies continue to run. The eraser/duplicator offers two modes of duplication: system and file and whole file.

The drive duplicator/eraser lets you erase up to seven flash drives at the same time, so it's easy to clean large batches of USB drives for reuse. The flash drive duplicator features three modes of erasing: quick erase, single pass erase, and multi-pass erase (meets DoD standards).

The flash drive duplicator and eraser supports USB 3.0, USB 2.0 and USB 1.1 flash drives, providing an easy and cost-effective way to re-use and re-purpose your USB drives. It features a robust metal housing and a compact, standalone design that makes it the perfect desktop companion. The duplicator/eraser also has an LCD display that makes it easy to monitor erasing and duplication to ensure completion.

The USBDUPE17 is TAA compliant and backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Software and operating system update rollouts
- Marketing collateral copying and distribution
- Backup USB flash drives without a host computer
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- IT administrators who wish to erase multiple drives simultaneously in preparation for use in other applications

Features

- Duplicate or erase up to seven USB 3.0, USB 2.0 and USB 1.1 flash drives, without connecting to a host computer
- 1:7 standalone duplication with two duplication modes: system and file, and whole file
- Erase up to seven drives at the same time, with three modes: quick erase, single pass erase, and multi-pass erase (meets DoD standards)
- TAA compliant
- Compact metal design
- Built-in LCD display
- Duplication speeds up to 1.5GB per minute
- Supports both asynchronous and synchronous copy modes, for quick batch swapping with 64 MB of internal memory
- Includes universal power adapter

Hardware	Warranty	2 Years
	Bus Type	USB 2.0
	Number of Drives	7
	Compatible Drive Types	USB Flash Drive
	Drive Installation	Removable
	Chipset ID	Xilinx - Spartan (XC3S700A)
	Buffer Size	128 MB
	Performance	Duplication Modes
Duplication Modes		Sector by Sector (Whole Drive)
Duplication Speed		1.5GBpm
Erase Modes		Quick Erase
Erase Modes		1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)
Erase Modes		3-Pass Overwrite
Max Drive Capacity		Maximum drive size of 2TB
Insertion Rating		1500 times
MTBF		176,549 hours

Connector(s)	Drive Connectors	USB Type-A (4 pin) USB 2.0
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	System and Cable Requirements	For duplication, the destination drives must be of equal or greater capacity than the source drive.
	System and Cable Requirements	Supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure (sold separately)
Indicators	LED Indicators	Green (Activity/Successful Copy)
	LED Indicators	Red (Error)
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	1.6A Max
	Output Voltage	12V DC
	Output Current	9A
	Plug Type	4-pin DIN
	Power Consumption (In Watts)	108W
Environmental	Operating Temperature	5C ~ 45C (41F ~ 113F)
	Storage Temperature	-20C ~85C (-4F ~ 185F)
	Humidity	20% ~ 80%
Physical Characteristics	Color	Black
	Material	Steel
	Product Length	7.5 in [1.9 cm]
	Product Width	6.3 in [1.6 cm]
	Product Height	1.4 in [34.6 mm]
	Weight of Product	2.3 lb [1.0 kg]
Packaging Information	Package Length	17.5 in [4.4 cm]
	Package Width	9.3 in [2.4 cm]
	Package Height	3.3 in [85 mm]

Shipping (Package)
Weight 6.5 lb [3.0 kg]

**What's in the
Box**

Included in Package	duplicator and eraser
Included in Package	universal power adapter (NA/JP, UK, EU, ANZ)
Included in Package	instruction manual

****Product appearance and specifications are subject to change without notice.***

