

1ft (30cm) Heavy Duty Power Cord, Twist-Lock NEMA L5-15P to NEMA 5-15R Black Adapter Cord, 15A 125V, 14AWG, Heavy Gauge Plug Converter Cable, TAA Compliant, UL Listed

Produkt-ID: W31C-4100-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Heavy Duty power cord supports high-powered equipment and PDUs
- Extend a server or rackmount equipment power cord by an additional 2ft

Merkmale

- **HEAVY DUTY ADAPTER CABLE:** 1ft (30cm) Adapter Power Cable with Twist-Lock NEMA L5-15P to NEMA 5-15R connector works with servers or high-power equipment; Locking L5-15 plug securely attaches to an outlet or power source; Indoor use; Rated up to 125V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 1ft (30cm); TAA Compliant; Twist-Lock NEMA L5-15P to NEMA 5-15R; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA L5-15P to NEMA 5-15R power cord works with North American PDUs and high-powered devices; Convert a NEMA L5-15 outlet to 5-15R for convenient integration with servers, switches, or UPS; Heavy duty adapter power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, the heavy duty adapter power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This adapter power cable is available in other plug configurations

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC
Feuerwiderstandssklass	Klasse VW-1

e

Kabeltyp SJT

Leistung

Max. Kabellänge 1.0 ft [0.3 m]

Steckverbinder

Steckverbinder A 1 - NEMA L5-20P (North America)

Steckverbinder B 1 - NEMA 5-15 Strom (Nordamerika)

Strom

Ausgangsstrom 15A

Umgebungsbedingungen

Betriebstemperatur -20° to 105°C (-4° to 221°F)

Lagertemperatur -20° to 105°C (-4° to 221°F)

Feuchtigkeit 0% to 65% RH

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 14 AWG

Kabellänge 1.0 ft [0.3 m]

Außendurchmesser des Kabels 0.4 in [9.3 mm]

Produktlänge 12.0 in [30.5 cm]

Produktbreite 1.5 in [3.9 cm]

Produkthöhe 1.5 in [3.9 cm]

Produktgewicht 5.7 oz [162.0 g]

Verpackungsinformationen

Paketlänge 6.9 in [17.4 cm]

Paketbreite	5.7 in [14.5 cm]
Pakethöhe	1.7 in [4.2 cm]
Versandgewicht (Verpackung)	6.2 oz [176.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 30cm NEMA 5-15R auf NEMA L5-15P Hochleistungs-Netzkabel
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.